




0077384A7

110 Delta Drive
Pittsburgh, PA 15238
NAFTA Sales: (1)800-245-3984
HK Sales : (852)3102-9337
magnetics@spang.com
www.mag-inc.com



Kool Mμ Permeability (μ)	A _L (nH/T ²)	Core Marking			Coating Color
		Lot Number	Part Number	Inductance Grade	
90	64 ± 8%	XXXXXX	77384A7	N/A	Black

Dimensions	Uncoated		Coated Limits			Packaging Bulk Pack 4 bags/box Box Qty= 2000 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	17.27	0.680	18.03	0.710	max	
ID (B)	9.65	0.380	9.02	0.355	min	
HT (C)	6.35	0.250	7.11	0.280	max	

Electrical Characteristics			Physical Characteristics						
Watt Loss @ 100 kHz, 100mT max (mW/cm³)	DC Bias min (oersteds)		Voltage Breakdown wire to wire min (V _{AC})	Break Strength min (kg)	Window Area W _A (mm²)	Cross Section A _e (mm²)	Path Length L _e (mm)	Volume V _e (mm³)	Weight (g)
750	80%	50%	>2000	28.0	63.8	23.2	41.4	960	5.7230
	21.0	52.0							

Winding Information					Temperature Rating	
Winding Length Per Turn				Wound Coil Dimensions (mm)		Curie Temp: 500°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	19.6
					HT	10.1
				Completely Full Window	Max OD	24.9
					Max HT	16.3
0%	23.2	40%	28.0	Surface Area (mm ²)		
20%	25.6	45%	28.6			
25%	26.2	50%	29.3	Unwound Core		
30%	26.6	60%	30.8	990		
35%	27.4	70%	32.4	40% Winding Factor		
				1,400		

Typical DC Bias Performance

