

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight panel cable jack (female), flange mount

25_BNC-50-2-1/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration

Gender	Standard
jack	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Operating frequency	4 GHz

Mechanical data

Weight	0.0188 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	clamped

Environmental data

Operation temperature	-65 °C ... 165°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
22540424	25_BNC-50-2-1/133_NE	Single

Suitable cables

Cable group	X3 - 2 mm / 50 Ohm U2 - 2 mm / 50 Ohm
-------------	--

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight panel cable jack (female), flange mount

25_BNC-50-2-1/133_N

Additional Information

Only as assembly

No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2511 / Date of publication: 16.10.2023 / uncontrolled copy