

# FOC-ADAPTER:LCD/LCD-OM4 - Fiber optic coupling

1208072

<https://www.phoenixcontact.com/us/products/1208072>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic coupling, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight, color: violet, Ethernet

## Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Versatile range of applications with an extended temperature range and various mounting options
- Optimum compatibility with the FDX20 series splice boxes
- Future-proof, thanks to RoHS 2 conformity

## Commercial data

Item number	1208072
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4063151277000
Weight per piece (including packing)	5 g
Weight per piece (excluding packing)	5 g
Customs tariff number	85367000
Country of origin	CN

# FOC-ADAPTER:LCD/LCD-OM4 - Fiber optic coupling

1208072

<https://www.phoenixcontact.com/us/products/1208072>



## Technical data

### Product properties

Product type	Female insert
Type	LC
Sensor type	Ethernet
Number of positions	2
Connection profile	LC
Number of slots	2
Cable outlet	straight

### Data management status

Article revision	00
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated surge voltage	0.8 kV
Attenuation	≤ 0.2 dB
Nominal current $I_N$	0.5 A
Transmission medium	FO

### Connection data

Connection technology	
Connection method	Coupling

### Dimensions

Width	22 mm
Height	9.4 mm
Length	29.2 mm

### Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

### Material specifications

Color	violet
Color of the housing part	violet
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy

### Cable/line

Cable type	Fiberglass
------------	------------

# FOC-ADAPTER:LCD/LCD-OM4 - Fiber optic coupling

1208072

<https://www.phoenixcontact.com/us/products/1208072>



External sheath, color	beige
Tensile strength short-term/long-term	40 N
Flame resistance	yes
FO cable	
Number of fibers	2
Fiber	50/125 µm
Fiber type	Fiberglass

## Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

## Characteristics

Attenuation	≤ 0.2 dB
-------------	----------

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to UV radiation	no

## Standards and regulations

Flame resistance	yes
------------------	-----

# FOC-ADAPTER:LCD/LCD-OM4 - Fiber optic coupling

1208072

<https://www.phoenixcontact.com/us/products/1208072>



## Classifications

### ECLASS

ECLASS-11.0	27440392
ECLASS-13.0	19170116
ECLASS-12.0	27440392

### ETIM

ETIM 9.0	EC000752
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FOC-ADAPTER:LCD/LCD-OM4 - Fiber optic coupling

1208072

<https://www.phoenixcontact.com/us/products/1208072>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)