

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

H distributor, 5-position, shielded, Plug straight M12, coding: L, on Socket straight M12, coding: L and Socket straight M12, coding: L, for direct current up to 16 A/63 V, Parallel distributor



## Your advantages

- High-performance: DC connectors for up to 16 A and 63 V DC

## Commercial data

Item number	1080248
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	BF1GAP
GTIN	4055626802817
Weight per piece (including packing)	131.3 g
Weight per piece (excluding packing)	131.3 g
Customs tariff number	85366990
Country of origin	DE

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Notes on the product family	UL approval in preparation

### Product properties

Product type	H-distributor
Application	Power supply
Number of positions	5
No. of cable outlets	3
Shielded	yes
Coding	L
Thread type	M12

### Data management status

Article revision	00
------------------	----

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	63 V DC
Nominal current $I_N$	16 A (at 40 °C)

### Signaling

Status display	no
Status display present	No

### Dimensions

Dimensional drawing	
Width	28 mm
Height	47 mm
Length	80 mm
Center distance	35 mm

### Material specifications

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



Material	CuZn (Pin contact) (Female contact)
Flammability rating according to UL 94	V0
Seal material	HNBR
Material of grip body	PBT
Contact surface material	Au
Contact carrier material	PBT
Material for screw connection	Brass, nickel-plated

## Connector

### Connection 1

Type	Plug straight M12
Coding type	L

### Connection 2

Type	Socket straight M12
Coding type	L

### Connection 3

Type	Socket straight M12
Coding type	L

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor


1080248

<https://www.phoenixcontact.com/us/products/1080248>




## Drawings

Circuit diagram



Dimensional drawing



M12 H-distributor


# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>




Schematic diagram



Pin assignment of M12 connector, 5-pos., L-coded, pin side view

Diagram



Current carrying capacity


# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



## Classifications

### ECLASS

ECLASS-11.0	27440106
ECLASS-12.0	27440106
ECLASS-13.0	27440106

### ETIM

ETIM 9.0	EC002925
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-5PH-ML-FL/2XFL F VP SH - H distributor

1080248

<https://www.phoenixcontact.com/us/products/1080248>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)