

# SACC-M12-PPI NUT L 90 - Housing screw connection

1233779

<https://www.phoenixcontact.com/us/products/1233779>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M12 push-pull housing screw connection for M12 socket inserts, with flat gasket



## Your advantages

- Plug and Produce: quick and reliable connection even in confined spaces
- Easy design-in: countersunk M12 ports for compact device concepts
- Highly future-proof: standardized product range for worldwide availability
- Greater flexibility: one M12 device connection for screw and push-pull connectors

## Commercial data

Item number	1233779
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQAAH
GTIN	4063151337100
Weight per piece (including packing)	10.42 g
Weight per piece (excluding packing)	10.42 g
Customs tariff number	74198090
Country of origin	DE

# SACC-M12-PPI NUT L 90 - Housing screw connection

1233779

<https://www.phoenixcontact.com/us/products/1233779>



## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

### Product properties

Product type	Panel mounting base
Thread type	M12
Data management status	
Article revision	01

### Connection data

Connection method	THR solder connection
Tightening torque	1.5 ... 2 Nm

### Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Seal material	HNBR
	FKM
Material of grip body	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

### Connector

Connection 1	
Head design	Socket
Head thread type	M12
Head locking type	Push-pull internal locking

### Cable/line

Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation)
	-25 °C ... 85 °C (Cable, flexible installation)

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

### Environmental and real-life conditions

# SACC-M12-PPI NUT L 90 - Housing screw connection

1233779

<https://www.phoenixcontact.com/us/products/1233779>



## Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
	IP65, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
	-25 °C ... 85 °C (Cable, flexible installation)
	-40 °C ... 85 °C (cable, fixed installation)

## Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-010
Note	In line with

## Mounting

Mounting type	Front mounting M12 x 1
---------------	------------------------

# SACC-M12-PPI NUT L 90 - Housing screw connection

1233779

<https://www.phoenixcontact.com/us/products/1233779>



## Classifications

### ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

### ETIM

ETIM 9.0	EC003556
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-M12-PPI NUT L 90 - Housing screw connection

1233779

<https://www.phoenixcontact.com/us/products/1233779>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)