



CMC040025015H


110 Delta Drive
Pittsburgh, PA 15238
NAFTA Sales: (1) 800-245-3984
HK Sales: (852) 3102-9337
magnetics@spang.com
www.mag-inc.com

Dimensions				
	Bare (mm)	tol +/-	Case (mm)	tol +/-
OD (A)	40.0	typ	44.2	0.50
ID (B)	25.0	typ	21.6	0.50
HT (C)	15.0	0.20	18.9	0.50

A_L ($\mu\text{H}/\text{T}^2$)	Conditions	
101 +/- 30%	10 kHz	2 mT
23.1 min	100 kHz	2 mT

A_e (cm^2)	L_e (cm)	Weight (g)	Color
0.92	10.2	68.0 (Ref)	Black

PBT Class B 130°C



Material	Nanocrystalline
Saturation Flux Density	1.25 Tesla
Initial permeability	80,000
Curie Temperature	560 °C
Continuous working Temperature	-40 °C to +130 °C