




Specification for:  
**ZW44932TC**

110 Delta Drive  
 Pittsburgh, PA 15238  
 Phone: 412/696-1333  
 Fax: 412/696-0333  
 Email:magnetics@spang.com

**DIMENSIONS**



(mm)	Uncoated Nominal:	Coated Min:	Coated Max:
O.D. (A)	49.1	48.10	50.60
I.D. (B)	33.8	32.30	34.80
Ht. (C)	31.6	31.30	32.90

Eff. Parameters		
A <sub>e</sub> mm <sup>2</sup>	l <sub>e</sub> mm	V <sub>e</sub> mm <sup>3</sup>
239	127	30405

**INDUCTANCE**

AL value (nH/T <sup>2</sup> )	Test conditions
23600 ± 30%	10 kHz, 0.5 mT (For N = 5, use 0.60 mA), 25°C

**ELECTRICAL LOSSES**

tan δ / μ <sub>i</sub>	Production lot limit Average	Test conditions	
≤ 4.1 · 10 <sup>-6</sup>	≤ 3.5 · 10 <sup>-6</sup>	10 kHz	0.5 mT, 25°C
≤ 60 · 10 <sup>-6</sup>	≤ 50 · 10 <sup>-6</sup>	100 kHz	

**COATING**

Epoxy rated for 200°C continuous operation.
Voltage breakdown rating 2000 V Min Wire-to-Wire.

**NOTE**

Spec. Modifications	Previous	Revised
2006.01.13	Bare Nom Ht = 31.8 LF: General W material Breakdown voltage > 1000 V	Bare Nom Ht = 31.6 LF: Detail as indicated Breakdown voltage > 2000 V