


DIMENSIONS



(mm)	Uncoated Nominal:	Coated Min:	Coated Max:
O.D. (A)	7.62	7.29	7.95
I.D. (B)	3.18	2.84	3.52
Ht. (C)	4.78	4.58	4.98

Eff. Parameters		
$A_e \text{ mm}^2$	$l_e \text{ mm}$	$V_e \text{ mm}^3$
9.9	15	149

INDUCTANCE

AL value (nH/T ²)	Test conditions
2505± 20%	10 kHz, 0.5 mT (For N = 5, use 0.23 mA), 25°C

CORE LOSSES

$P_L \text{ max}$	Production lot limit Max avg	Test conditions
32.8mW (220 mW/cm ³)	29.8mW (200 mW/cm ³)	25 kHz, 200 mT, 100°C

COATING

Black lacquer
