

BL2 BPC 1501E-128-W10 - Box PC



1158235

<https://www.phoenixcontact.com/us/products/1158235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor with 32 GB eMMC mass storage, 128 GB M.2 SSD, 2x COM ports, and Windows 10 Enterprise 2019 LTSC operating system

Commercial data

Item number	1158235
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABA
GTIN	4063151163754
Weight per piece (including packing)	920 g
Weight per piece (excluding packing)	650 g
Customs tariff number	84715000
Country of origin	TW

BL2 BPC 1501E-128-W10 - Box PC

1158235

<https://www.phoenixcontact.com/us/products/1158235>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
--------------	--------

Data management status

Article revision	06
------------------	----

Computer data

Processor	Intel® Celeron® N3350 1.10/2.4 GHz
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
RAM	4 GB LPDDR4
Data storage system	eMMC internal, 32 GB 128 GB M.2 SSD
Cooling	passive

Display

Display type	none
--------------	------

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Maximum power dissipation for nominal condition	16.8 W
---	--------

Supply

Supply voltage (DC)	24 V DC (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

Connection data

Power supply

Connection method	Screw connection
Conductor cross section, rigid	0.14 mm² ... 1.5 mm²
Conductor cross section, flexible	0.14 mm² ... 1.5 mm²
Conductor cross section AWG	28 ... 16
Stripping length	7 mm

Interfaces

BL2 BPC 1501E-128-W10 - Box PC



1158235

<https://www.phoenixcontact.com/us/products/1158235>

Interfaces	1x DP++
	2x USB 3.0
	2x COM ports
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 63 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
	IP30
Ambient temperature (operation)	-20 °C ... 50 °C (with 0.5 m/s airflow)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
FCC	Title 47 Part 15 Subpart B:2018 Class A

Mounting

Mounting type	DIN rail mounting
	Wall mounting (Accessories required)

BL2 BPC 1501E-128-W10 - Box PC



1158235

<https://www.phoenixcontact.com/us/products/1158235>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1158235>



EAC-RoHS
Approval ID: RU*-DE*HB.B.00386/20



IECEE CB Scheme
Approval ID: US-39601-M1-UL



UL Listed
Approval ID: E238705 D12:D1050



cUL Listed
Approval ID: E238705 D12:D1050

cULus Listed

BL2 BPC 1501E-128-W10 - Box PC



1158235

<https://www.phoenixcontact.com/us/products/1158235>

Classifications

ECLASS

ECLASS-11.0	19200102
ECLASS-12.0	19200102
ECLASS-13.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)