




11.7 Volt Temperature Compensated Zener Reference Diodes

Qualified per MIL-PRF-19500/157

Qualified Levels:
JAN, JANTX,
JANTXV and JANS
(available on some part
numbers)

DESCRIPTION

The popular 1N941UR-1 thru 1N945BUR-1 series of zero-TC reference diodes provides a selection of 11.7 V nominal voltages and temperature coefficients to as low as 0.0002 %/°C for minimal voltage change with temperature when operated at 7.5 mA. Some of these glass, DO-213AA reference diodes are also available in JAN, JANTX, JANTXV and JANS military qualifications. Microsemi also offers numerous other Zener reference diode products for a variety of other voltages from 6.2 V to 200 V.



Important: For the latest information, visit our website <http://www.microsemi.com>.

FEATURES

- Surface mount equivalent of the JEDEC registered 1N941 thru 1N945 series.
- Standard reference voltage of 11.7 V +/- 5% with tighter reference tolerances of 1%, 2%, and 3% available on commercial level only.
- Internal metallurgical bond.
- JAN, JANTX, JANTXV and JANS qualification per MIL-PRF-19500/157 available on 1N941BUR-1, 1N943BUR-1, 1N944BUR-1, and 1N945BUR-1.
- RoHS compliant versions available (commercial grade only).

DO-213AA Package

Also available in:

DO-35 (DO-204AH)
(axial-leaded)

 [1N941-1 thru 1N945B-1](#)

APPLICATIONS / BENEFITS

- Provides minimal voltage changes over a broad temperature range.
- For instrumentation and other circuit designs requiring a stable voltage reference.
- Maximum temperature coefficient selections available from 0.01 %/°C to 0.0005 %/°C.
- Non-sensitive to ESD per MIL-STD-750, method 1020.

MAXIMUM RATINGS

| Parameters/Test Conditions | Symbol | Value | Unit |
|--|---------------------|-------------|------|
| Power Dissipation @ $T_L = 25$ °C and maximum current I_{ZM} of 39 mA. ^(1, 2) | P_D | 500 | mW |
| Junction and Storage Temp | T_J and T_{STG} | -55 to +175 | °C |
| Maximum Zener Current | I_{ZM} | 39 | mA |
| Solder Temperature @ 10 s | T_{SP} | 260 | °C |

Notes: 1. For optimum voltage-temperature stability, $I_Z = 7.5$ mA (less than 95 mW in dissipated power).
2. Derate at 3.33 mW/°C above $T_A = +25$ °C.

MSC – Lawrence

6 Lake Street,
Lawrence, MA 01841
Tel: 1-800-446-1158 or
(978) 620-2600
Fax: (978) 689-0803

MSC – Ireland

Gort Road Business Park,
Ennis, Co. Clare, Ireland
Tel: +353 (0) 65 6840044
Fax: +353 (0) 65 6822298

Website:


www.microsemi.com

MECHANICAL and PACKAGING


- CASE: Hermetically sealed glass case with surface mount DO-213AA (MELF, SOD-80, LL34) package.
- TERMINALS: Tin-lead plated or RoHS compliant matte-tin plating available (on commercial grade only) and solderable per MIL-STD-750, method 2026.
- MARKING: Cathode band.
- POLARITY: Reference diode to be operated with the banded end positive with respect to the opposite end.
- MOUNTING SURFACE SELECTION: The Axial Coefficient of Expansion (COE) of this device is approximately +6PPM/ $^{\circ}$ C. The COE of the mounting surface system should be selected to provide a suitable match with this device.
- TAPE & REEL option: Standard per EIA-481-B with 12 mm tape. Consult factory for quantities. (Add "TR" suffix to part number.)
- WEIGHT: 0.2 grams.
- See [Package Dimensions](#) on the last page.

PART NOMENCLATURE

Applicable to: JAN, JANTX, JANTXV and JANS level 1N941B, 1N943B, 1N944B, and 1N945B only:



Applicable to: Commercial level 1N941 thru 1N945B:



| SYMBOLS & DEFINITIONS | |
|-----------------------|---|
| Symbol | Definition |
| I_R | Reverse Current: The maximum reverse (leakage) current that will flow at the specified voltage and temperature. |
| I_Z, I_{ZT}, I_{ZK} | Regulator Current: The dc regulator current (I_Z), at a specified test point (I_{ZT}), near breakdown knee (I_{ZK}). |
| V_Z | Zener Voltage: The Zener voltage the device will exhibit at a specified current (I_Z) in its breakdown region. |
| V_{ZT} | Zener Voltage Temperature. |
| Z_{ZT} or Z_{ZK} | Dynamic Impedance: The small signal impedance of the diode when biased to operate in its breakdown region at a specified rms current modulation (typically 10% of I_{ZT} or I_{ZK}) and superimposed on I_{ZT} or I_{ZK} respectively. |

ELECTRICAL CHARACTERISTICS @ 25°C unless otherwise specified.

| JEDEC TYPE NUMBER (Notes 4) | ZENER VOLTAGE V_Z @ I_{ZT} (Note 3) | ZENER TEST CURRENT I_{ZT} | MAXIMUM ZENER IMPEDANCE Z_{ZT} @ I_{ZT} (Note 1) | MAXIMUM REVERSE CURRENT I_R @ 8 V | VOLTAGE TEMPERATURE STABILITY ΔV_{ZT} MAXIMUM (Note 2 & 3) | TEMPERATURE RANGE | EFFECTIVE TEMPERATURE COEFFICIENT α_{VZ} |
|--------------------------------------|--|--------------------------------------|--|--|---|----------------------|--|
| | Volts | mA | Ohms | μA | mV | °C | % / °C |
| 1N941UR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 88 | 0 to +75 | 0.01 |
| 1N941AUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 181 | -55 to +100 | 0.01 |
| 1N941BUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 239 | -55 to +150 | 0.01 |
| 1N942UR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 44 | 0 to +75 | 0.005 |
| 1N942AUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 90 | -55 to +100 | 0.005 |
| 1N942BUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 120 | -55 to +150 | 0.005 |
| 1N943UR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 18 | 0 to +75 | 0.002 |
| 1N943AUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 36 | -55 to +100 | 0.002 |
| 1N943BUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 47 | -55 to +150 | 0.002 |
| 1N944UR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 9 | 0 to +75 | 0.001 |
| 1N944AUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 18 | -55 to +100 | 0.001 |
| 1N944BUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 24 | -55 to +150 | 0.001 |
| 1N945UR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 4 | 0 to +75 | 0.0005 |
| 1N945AUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 9 | -55 to +100 | 0.0005 |
| 1N945BUR-1 | 11.12 - 12.28 | 7.5 | 30 | 15 | 12 | -55 to +150 | 0.0005 |

*JEDEC Registered Data.

NOTES:

1. Measured by superimposing 0.75 mA ac rms on 7.5 mA dc @ 25 °C.
2. The maximum allowable change observed over the entire temperature range i.e., the diode voltage will not exceed the specified mV change at any discrete temperature between the established limits.
3. Voltage measurements to be performed 15 seconds after application of dc current.
4. The 1N941BUR-1, 1N943BUR-1, 1N944BUR-1, and 1N945BUR-1 only are military qualified to MIL-PRF-19500/157 up to the JANS level.


GRAPHS


FIGURE 1
**TYPICAL CHANGE OF TEMPERATURE COEFFICIENT
 WITH CHANGE IN OPERATING CURRENT**

The curve shown in Figure 1 is typical of the diode series and greatly simplifies the estimation of the Temperature Coefficient (TC) when the diode is operated at currents other than 7.5 mA.

EXAMPLE: A diode in this series is operated at a current of 7.5 mA and has specified Temperature Coefficient (TC) limits of $\pm 0.002\text{ }^{\circ}\text{C}$. To obtain the typical Temperature Coefficient limits for this same diode operated at a current of 6.0 mA, the new TC limits ($\text{mV/}^{\circ}\text{C}$) can be estimated using the graph in Figure 1.

At a test current of 6.0mA the change in Temperature Coefficient (TC) is approximately $-0.0009\text{ }^{\circ}\text{C}$. The algebraic sum of $\pm 0.002\text{ }^{\circ}\text{C}$ and $-0.0009\text{ }^{\circ}\text{C}$ gives the new estimated limits of $+0.0011\text{ }^{\circ}\text{C}$ and $-0.0029\text{ }^{\circ}\text{C}$.




FIGURE 2
**TYPICAL CHANGE OF ZENER VOLTAGE
 WITH CHANGE IN OPERATING CURRENT**

This curve in Figure 2 illustrates the change of diode voltage arising from the effect of impedance. It is in effect, an exploded view of the Zener operating region of the I-V characteristic.

In conjunction with Figure 1, this curve can be used to estimate total voltage regulation under conditions of both varying temperature and current.


GRAPHS

FIGURE 3
POWER DERATING CURVE






FIGURE 4
TYPICAL ZENER IMPEDANCE VS. OPERATING CURRENT

PACKAGE DIMENSIONS

NOTES:

1. Dimensions are in inches.
2. Millimeters are given for general information only.
3. In accordance with ASME Y14.5M, diameters are equivalent to Φx symbology.

| | Inch | | Millimeter | |
|------------|-----------|-------|------------|------|
| DIM | MIN | MAX | MIN | MAX |
| BD | 0.063 | 0.067 | 1.60 | 1.70 |
| ECT | 0.016 | 0.022 | 0.41 | 0.56 |
| BL | 0.130 | 0.146 | 3.30 | 3.70 |
| S | 0.001 MIN | | 0.03 MIN | |

PAD LAYOUT


| DIM | INCH | MILLIMETER |
|----------|------|------------|
| A | .200 | 5.08 |
| B | .055 | 1.40 |
| C | .080 | 2.03 |