



# SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃


Contact Material:Brass

Contact Plating:Au or Sn Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds  
(260℃ for 10 seconds)



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



## Ordering Information

2372 02 XX X N XX R U X 0X

No.of  
Pins  
Per Row  
2\*40

Insulator Material


Option  
A=BK-PBT  
B=BK-PA66  
C=BK-PA6T  
D=BK-PA46  
F=BK-LCP

Contact Plating

G1:Gold Flash  
G2:1.5U" Gold  
G3:2U" Gold  
G4:3U" Gold  
G5:5U" Gold  
S0:Gold Flash/Tin  
SN:Tin

Packing

0=PE Bag  
A=Tray  
T=Tube  
P=Tube+Cap  
R=Reel+Cap  
M=Reel+Mylar



OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

YiYuSheng

12.04.18

SCALE

FIT

UNIT mm

SIZE A4

SHEET 1/1

PROJ.

**JILN** 深圳市锦凌电子有限公司  
SHENZHEN JINLING ELECTRONIC CO.,LTD

Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

PART NO.

237202XXXXXRXUX0X

TITLE:

2.00PF H7.2mm 2xNpin 90°

A0 2012.04.18 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE