

DO NOT
SCALE FROM
THIS PRINTDESIGNED & DIMENSIONED IN MILLIMETERS
(INCHES FOR REFERENCE ONLY)

MEC2-XX-XX-X-XXX-XX-X-XX

No OF POSITIONS (PER ROW)

-05, -08, -20, -30, -40, -50
(SEE TABLE 2 FOR POSITION
REMOVED TO POLARIZE)

CARD THICKNESS

-01: 1.57mm [.062"] THICK
-02: 2.36mm [.093"] THICK

PLATING SPECIFICATION

-L: 10μ" LIGHT SELECTIVE GOLD
IN CONTACT AREA MATTE
TIN ON TAIL

ROW SPECIFICATION

-DV: SURFACE MOUNT
-TH1: THROUGH HOLE FOR
1.57mm [.062"] THICK BOARD
□-TH2: THROUGH HOLE FOR
2.36mm [.093"] THICK BOARD
(□ = NOT RELEASED)

PACKAGING (SEE NOTES 8 & 9)

BLANK: TUBES (SEE NOTE 7)

-TR: TAPE & REEL (-05 THRU -30 POS ONLY)

AVAILABLE WITH -DV ONLY

-FR: FULL REEL QTY TAPE & REEL

(-05 THRU -30 POS ONLY)

AVAILABLE WITH -DV ONLY

PICK & PLACE PAD

-K: POLYIMIDE FILM PAD

(SEE SHT 2, TABLE 6) AVAILABLE WITH -DV & -T ONLY
(-05 THRU -30 POS ONLY)

OPTION

-NP: NON-POLARIZED

(-05, -08, -20 & -30 POSITIONS ONLY)

(USE MEC2-XX-XX-TH-NP) (SEE FIG 4, SHT 3)

-WT: WELD TABS

(REQUIRED ON -02 CARD THICKNESS)

(OPTIONAL ON -01 CARD THICKNESS)

(SEE FIG 2, SHT 2)




DETAIL 'B'
SCALE 8 : 1

FIG 1

NOTES:

(MEC2-08-01-XX-DV-XX SHOWN)

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. BURR ALLOWANCE: 0.04[.0015] MAX.
3. MINIMUM PUSHOUT FORCE: 2.2 NEWTONS [.50LBS.]
4. ALL TAIL TO TAIL DIMENSIONS MEASURED TIP TO TIP.
5. NOTE DELETED.
6. MATING EDGE CARD THICKNESS TOLERANCE NOT TO EXCEED ±10%
7. TUBES ARE STANDARD PACKAGING.
8. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM
9. ATTACH LABEL TO EACH REEL




TABLE 2

No OF POS	POLARIZED POSITIONS
**05	3, 4
**08	5, 6
**20	15, 16
**30	21, 22
**40	31, 32
**50	41, 42

(**=NUMBER OF POSITIONS WILL
BE REDUCED BY 1 PER ROW FOR
POLARIZATION)

TABLE 1

No OF POS	COPLANARITY
-05 THRU -30	0.102 [.0040]
-40 & -50	0.152 [.0060]

TABLE 3

No. OF POS. PER ROW	"A"	"B"	"C"	"D"	"E"
-05	13.40 [.528]	11.50 [.453]	11.14 [.439]	8.00 [.315]	2.77 [.109]
-08	19.40 [.764]	17.50 [.689]	17.14 [.675]	14.00 [.551]	4.77 [.188]
-20	43.40 [1.709]	41.50 [1.634]	41.14 [1.620]	38.00 [1.496]	14.77 [.581]
-30	63.40 [2.496]	61.50 [2.421]	61.14 [2.407]	58.00 [2.283]	20.77 [.818]
-40	83.40 [3.283]	81.50 [3.209]	81.14 [3.194]	78.00 [3.071]	30.77 [1.211]
-50	103.40 [4.071]	101.50 [3.996]	101.14 [3.982]	98.00 [3.858]	40.77 [1.605]
No. OF POS. PER ROW	"F"	"G"	"H"	"J"	"K"
-05	N/A	4.000 [.1575]	N/A	4.00 [.157]	8.00 [.315]
-08	2.000 [.0787]	6.000 [.2362]	2.00 [.079]	6.00 [.236]	14.00 [.551]
-20	12.000 [.4724]	16.000 [.6299]	12.00 [.472]	16.00 [.630]	38.00 [1.496]
-30	18.000 [.7087]	22.000 [.8661]	18.00 [.709]	22.00 [.866]	58.00 [2.283]
-40	28.000 [1.1024]	32.000 [1.2598]	28.00 [1.102]	32.00 [1.260]	78.00 [3.071]
-50	38.000 [1.4961]	42.000 [1.6535]	38.00 [1.496]	42.00 [1.654]	98.00 [3.858]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES ARE:

DECIMALS

.X: ±.3 [.01]

.XX: ±.13 [.005]

.XXX: ±.051 [.0020]

ANGLES

2°

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:

DO NOT SCALE DRAWING

SHEET SCALE: 1:0.4

INSULATOR: LCP, UL 94 V0

COLOR: -01 CARD THICKNESS BLACK,

-02 CARD THICKNESS NATURAL

CONTACT: BeCu ALLOY

F:\DWG\MISC\MKTG\MEC2-XX-XX-X-XXX-XX-X-XX-MKT.SLDDRW

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

MEC2 2.0mm EDGE CARD ASSEMBLY

DWG. NO.

MEC2-XX-XX-X-XXX-XX-X-XX

BY: KNOWLDEN

2/14/10

SHEET 1 OF 3




FIG 2
(MEC2-05-02-XX-DV-WT SHOWN)
(SAME AS FIG. 1, EXCEPT AS SHOWN)

TABLE 4					
CARD THICKNESS	"N"	"P"	"R"	"S"	"V"
-01 (.062 in)	5.60 [.220]	1.89 [.074]	0.55 [.022]	4.66 [.183]	3.02 [.119]
-02 (.093 in)	6.30 [.248]	2.68 [.106]	1.34 [.053]	5.45 [.215]	3.81 [.150]

TABLE 5		
No. OF POS. PER ROW	"L"	"M"
-05	17.40 [.685]	15.40 [.606]
-08	23.40 [.921]	21.40 [.843]
-20	47.40 [1.866]	45.40 [1.787]
-30	67.40 [2.654]	65.40 [2.575]
-40	87.40 [3.441]	85.40 [3.362]
-50	107.40 [4.228]	105.40 [4.150]

F:\DWG\MISC\MKTG\MEC2-XX-XX-X-XXX-XX-X-MKT.SLDDRW





FIG 3
-K OPTION
(MEC2-08-01-XX-DV-K SHOWN)

TABLE 6							
BOARD THICKNESS	W DIA.	"T"	"Q"				
			No OF POSITIONS PER ROW				
			-05	-08	-20	-30	KAPTON CALL-OUT
-01	5.00 [.197]	0.30	4.20 [.165]	7.20 [.283]	19.20 [.756]	29.20 [1.150]	K-DOT-.197-.344-.005
-02	6.00 [.236]	0.15	3.70 [.146]	6.70 [.264]	18.70 [.736]	28.70 [1.130]	K-DOT-.236-.343-.005
-01 WITH -WT	5.00 [.197]	0.30	6.20 [.244]	9.20 [.362]	21.20 [.835]	31.20 [1.228]	K-DOT-.197-.344-.005
-02 WITH -WT	6.00 [.236]	0.15	5.70 [.224]	8.70 [.343]	20.70 [.815]	30.70 [1.209]	K-DOT-.236-.343-.005

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
MEC2 2.0mm EDGE CARD ASSEMBLY
DWG. NO.
MEC2-XX-XX-X-XXX-XX-X-XX
BY: KNOWLDEN 2/14/10 SHEET 2 OF 3




FIG 4
(MEC2-08-01-XX-XXX-NP SHOWN)
(SAME AS FIG. 1, EXCEPT AS SHOWN)




FIG 5
SCALE 1:1
(MEC2-50-01-XX-DV-XX SHOWN)
(SAME AS FIG 1, EXCEPT AS SHOWN)
(SOME CENTER FEATURES REMOVED FOR CLARITY)







FIG 7
SCALE 3:1
MEC2-08-01-L-TH1-XX SHOWN
(SAME AS FIG 1, EXCEPT AS SHOWN)

TABLE 7		
ROW SPECS	"U"	CONTACT
-TH1	2.10 [.083]	C-411-01-L
-TH2	2.90 [.114]	C-411-02-L



PACKAGING VIEW

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 5:2



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
MEC2 2.0mm EDGE CARD ASSEMBLY

DWG. NO.
MEC2-XX-XX-X-XXX-XX-X-XX

BY: KNOWLDEN 2/14/10 SHEET 3 OF 3