

CSS 1.5-1/3 - Speed starter



1201511

<https://www.phoenixcontact.com/us/products/1201511>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 1.5 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input

Commercial data

Item number	1201511
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C473
Product key	CK7312
GTIN	4063151265700
Weight per piece (including packing)	1,340 g
Weight per piece (excluding packing)	1,340 g
Customs tariff number	85371098
Country of origin	CN

CSS 1.5-1/3 - Speed starter

1201511

<https://www.phoenixcontact.com/us/products/1201511>



Technical data

Product properties

Product type	Speed starter
Product family	CONTACTRON
Operating elements	Push button
	Rotary switch

Data management status

Article revision	03
------------------	----

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Number of phases	1
------------------	---

Input data

Mains

Number of phases	1
Input voltage	230 V AC
	240 V AC
Input voltage range	110 V AC ... 240 V AC -15 % ... +10 %
Frequency range	47 Hz ... 63 Hz
Nominal current	15.8 A (no line reactor)
	14.5 A (with line reactor)

Output data

Nominal motor power	1.5 kW
Apparent power	3 kVA
Nominal output current (I_N)	7.5 A (4 kHz)
	6.2 A (8 kHz)
	4.1 A (16 kHz)
Output frequency	0 Hz ... 500 Hz
Power dissipation	67 W (2 kHz)
	74 W (4 kHz)
	70 W (8 kHz)
	66 W (16 kHz)
	9 W (stand by)
Output current	≤ 11.25 A (180 s)
	≤ 5.625 A (180 s, during recovery time)
	≤ 13.5 A (15 s)
	≤ 3.75 A (15 s, during recovery time)
Recovery time	150 s (180 s)

CSS 1.5-1/3 - Speed starter



1201511

<https://www.phoenixcontact.com/us/products/1201511>

Overload time	12 s (15 s)
	30 s (180 s)
	3 s (15 s)
Discharge time	3 min (Intermediate circuit capacitors)

Switching

Output name	Relay output
Contact switching type	1 changeover contact
Maximum switching voltage	125 V AC
	30 V DC
Maximum inrush current	3 A
Inrush current, minimum	10 mA (5 V DC)

Connection data

Power-level terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross section rigid	0.2 mm ² ... 6 mm ²
Conductor cross section flexible	0.2 mm ² ... 6 mm ²
	0.2 mm ² ... 4 mm ² (with ferrule)
Conductor cross section AWG	24 ... 10

Control terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross section rigid	0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross section flexible	0.2 mm ² ... 1.5 mm ²
	0.2 mm ² ... 0.75 mm ²
Conductor cross section AWG	24 ... 16

Dimensions

Drill hole

Diameter	5.5 mm
Width	45 mm
Height	210 mm
Depth	190 mm
Length	≤ 50 m (EMC compliance category C2)
	≤ 50 m (EMC compliance category C3)
	≤ 50 m (no EMC compliance)

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

CSS 1.5-1/3 - Speed starter



1201511

<https://www.phoenixcontact.com/us/products/1201511>

Ambient conditions

Degree of protection (IP)	IP20
Degree of protection (NEMA)	NEMA 1
Ambient temperature (operation)	-20 °C ... 55 °C (without current derating)
	-20 °C ... 60 °C (with linear current derating)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Altitude	≤ 2000 m
	> 2000 m (with derating)
Permissible humidity (operation)	90 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)
Shock (operation)	15g, 11 ms
Vibration (operation)	0,075 mm / 1g
Air pressure (operation)	86 kPa ... 106 kPa
Air pressure (storage/transport)	70 kPa ... 106 kPa

Approvals

Safety Integrity Level (SIL, IEC 61800-5-2)

Identification	3
----------------	---

Performance Level (EN ISO 13849)

Identification	e
----------------	---

Category (ISO 13849)

Identification	4
----------------	---

Standards and regulations

Standards/regulations	IEC 61800-5-1
	IEC 61800-3

Mounting

Mounting type	DIN rail mounting
	Wall mounting

CSS 1.5-1/3 - Speed starter



1201511

<https://www.phoenixcontact.com/us/products/1201511>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1201511>



UL Listed
Approval ID: FILE E 322526



cUL Listed
Approval ID: FILE E 322526



Functional Safety
Approval ID: 01/205/5866.01/23



Functional Safety
Approval ID: 01/205/5866.01/23



Functional Safety
Approval ID: Reg01/205/5866.01/23

cULus Listed

CSS 1.5-1/3 - Speed starter



1201511

<https://www.phoenixcontact.com/us/products/1201511>

Classifications

ECLASS

ECLASS-11.0	27142320
ECLASS-13.0	27142320
ECLASS-12.0	27142320

ETIM

ETIM 9.0	EC000256
----------	----------

UNSPSC

UNSPSC 21.0	26111500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
	Bis(2-(2-methoxyethoxy)ethyl)ether(CAS: 143-24-8)
SCIP	70312783-fae6-4d56-9ded-93b580390144