


DIMENSIONS



(mm)	Uncoated Nominal:	Min:	Max:
O.D. (A)	5.84	5.55	6.13
I.D. (B)	3.05	2.76	3.34
Ht. (C)	3.18	2.93	3.43
Eff. Parameters			
Ae mm²	le mm	Ve mm³	
4.28	13.0	55.8	

INDUCTANCE

AL value (nH/T²)	Test conditions
1200 ± 25%	10 kHz, 0.5 mT (For N=1, use 0.204 mA), 25°C

CORE LOSSES

P_i max	Test conditions
< 29 mW (< 520 mW/cm ³)	100 kHz, 200 mT, 25 °C
< 27 mW (< 484 mW/cm ³)	100 kHz, 200 mT, 100 °C

COATING

Uncoated

NOTE

Spec. modifications	Previous	Revised
2016-01-28		Issued