




0077620A7

110 Delta Drive
Pittsburgh, PA 15238
NAFTA Sales: (1)800-245-3984
HK Sales : (852)3102-9337
magnetics@spang.com
www.mag-inc.com



Kool M μ Permeability (μ)	A_L (nH/T ²)	Core Marking			Coating Color
		Lot Number	Part Number	Inductance Grade	
125	394 $\pm$ 8%	XXXXXX	77620A7	N/A	Black

Dimensions	Uncoated		Coated Limits			Packaging Cardboard cut-outs Box Qty= 45 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	61.98	2.440	63.09	2.484	max	
ID (B)	32.59	1.283	31.70	1.248	min	
HT (C)	24.99	0.984	25.91	1.020	max	

Electrical Characteristics			Physical Characteristics						
Watt Loss @ 100 kHz, 100mT max (mW/cm³)	DC Bias min (oersteds)		Voltage Breakdown wire to wire min (V _{AC})	Break Strength min (kg)	Window Area W _A (mm²)	Cross Section A _e (mm²)	Path Length L _e (mm)	Volume V _e (mm³)	Weight (g)
1000	80%	50%	3000	193.0	789	360	144	51,800	320
	14	35							

Winding Information							Temperature Rating		
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: 500°C		
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	75.3	Coating Temp (Continuous up to): 200°C		
					HT	39.7			
				Completely Full Window	Max OD	81.4	Notes:		
					Max HT	47.4			
0%	83.0	40%	99.5	Surface Area (mm²)					
20%	91.3	45%	102						
25%	93.4	50%	104						
30%	94.9	60%	109	Unwound Core		12,000			
35%	97.5	70%	115	40% Winding Factor		21,000			

Typical DC Bias Performance

