

COIL: 26.5 VDC	
WINDING #1	WINDING #2
1000 OHMS ± 10% @ 25° C	1000 OHMS ± 10% @ 25° C
13.0 VDC MUST OPERATE	13.0 VDC MUST OPERATE
26.5 VDC NOMINAL VOLTAGE	26.5 VDC NOMINAL VOLTAGE

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 20 g's


SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 5 MS MAX  
BOUNCE 2.0 MS MAX

### CUSTOMER DATA SHEET

CONTACTS WILL SWITCH WHEN EITHER COIL IS ENERGIZED WITH POLARITY SHOWN



CONTACT RATING: LOW LEVEL TO 2 AMPS  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 11/2/93 | CK. 11/3/93



CUST. C. I. I. STD.  
 CUST. NO. \_\_\_\_\_

TYPE "LS" RELAY

LSBW-2C-24A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[LSBW-2C-24A](#)