

BL2 BPC 1501S-W - Box PC

1141904

<https://www.phoenixcontact.com/us/products/1141904>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor, 32 GB eMMC mass storage, and Wi-Fi

Commercial data

Item number	1141904
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBABA
GTIN	4063151101800
Weight per piece (including packing)	774 g
Weight per piece (excluding packing)	614 g
Customs tariff number	84715000
Country of origin	TW

BL2 BPC 1501S-W - Box PC

1141904

<https://www.phoenixcontact.com/us/products/1141904>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
--------------	--------

Data management status

Article revision	06
------------------	----

Computer data

Processor	Intel® Celeron® N3350 1.10/2.4 GHz
Operating system	without operating system
RAM	2 GB LPDDR4
Data storage system	eMMC internal, 32 GB
Cooling	passive

Display

Display type	none
--------------	------

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Maximum power dissipation for nominal condition	16.8 W
---	--------

Supply

Supply voltage (DC)	24 V DC (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

Connection data

Power supply

Connection method	Screw connection
Conductor cross section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	7 mm

Interfaces

1x DP++

BL2 BPC 1501S-W - Box PC



1141904

<https://www.phoenixcontact.com/us/products/1141904>

Interfaces	2x USB 3.0
	1x Wireless LAN
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 46 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
	IP30
Ambient temperature (operation)	-20 °C ... 50 °C (with 0.5 m/s airflow)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
FCC	Title 47 Part 15 Subpart B:2018 Class A

Mounting

Mounting type	DIN rail mounting
	Wall mounting (Accessories required)

BL2 BPC 1501S-W - Box PC



1141904

<https://www.phoenixcontact.com/us/products/1141904>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1141904>



UL Listed
Approval ID: E238705 D12:D1050



cUL Listed
Approval ID: E238705 D12:D1050



IECEE CB Scheme
Approval ID: US-39601-M1-UL

cULus Listed

BL2 BPC 1501S-W - Box PC



1141904

<https://www.phoenixcontact.com/us/products/1141904>

Classifications

ECLASS

ECLASS-11.0	19200102
ECLASS-12.0	19200102
ECLASS-13.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
	Lead(CAS: 7439-92-1)
SCIP	bc045017-a05f-4c8a-aaeb-470f70c9ced3