


DIMENSIONS



(mm)	Nominal:	Tol. min.:	Tol. max.:
A	35.56	-0.5	+ 0.5
B	3.68	-0.3	+ 0.3
C	17.8	-0.4	+ 0.4
Eff. Parameters (with 0_43618EC)			
Ae mm²	Amin mm²	le mm	Ve mm³
135.0	135.0	37.4	5060

INDUCTANCE

MARKING

AL value (nH/T²)	Test conditions (with 0P43618EC)	
Nom: 7736 Min.: 5802	10 kHz, < 0.5 mT, 25 °C	0P43618IC PXXXXX

CORE LOSSES

P_i max	Test conditions
120 mW/cm ³ (0.61 W/set)	100 kHz, 100 mT, 100 °C

NOTE

Spec. modifications	Previous	Revised
2005-06-22	AL=6382 Min. Losses: General P material	AL=5802 Min. Losses: Detail as indicated