

TO-263-2L Plastic-Encapsulate Diode

SBDB3045CT SCHOTTKY BARRIER RECTIFIER


MAIN CHARACTERISTICS

| | |
|--------------|-------------------------------------|
| I_o | 30 (2×15) A |
| V_{RRM} | 45V |
| T_j | 150 °C |
| $V_{F(typ)}$ | 0.57V (@T_j=125°C) |


FEATURES

- Low Power Loss, High Efficiency
- Guard Ring Die Construction for Transient Protection
- High Current Capability and Low Forward Voltage Drop

MARKING



SBDB3045CT = Device code
 Solid dot = Green molding compound device
 if none, the normal device
 XXXX = Code



MAXIMUM RATINGS (T_a=25°C unless otherwise noted)

| Symbol | Parameter | Value | Unit |
|-----------------|--|----------|------|
| V_{RRM} | Peak repetitive reverse voltage | 45 | V |
| V_{RWM} | Working peak reverse voltage | | |
| V_R | DC blocking voltage | | |
| $V_{R(RMS)}$ | RMS reverse voltage | 31.5 | V |
| I_o | Average rectified output current | 30 | A |
| I_{FSM} | Non-Repetitive peak forward surge current (8.3ms half sine wave) | 250 | A |
| $R_{\theta Jc}$ | Thermal resistance from junction to case , T _c =25°C | 2.0 | °C/W |
| $R_{\theta JA}$ | Thermal resistance from junction to ambient | 62.5 | °C/W |
| T_j | Junction temperature | 150 | °C |
| T_{stg} | Storage temperature | -55~+150 | °C |


ELECTRICAL CHARACTERISTICS (T_a=25°C unless otherwise specified)

| Parameter | Symbol | Test conditions | Min | Typ | Max | Unit |
|-----------------|------------|-----------------|-----------------------|------|------|------|
| Reverse voltage | $V_{(BR)}$ | $I_R=1mA$ | 45 | | | V |
| Reverse current | I_R | $V_R=45V$ | T _j =25°C | 8 | 50 | uA |
| | | | T _j =125°C | 14 | | mA |
| Forward voltage | V_F | $I_F=10A$ | T _j =25°C | 0.55 | | V |
| | | | T _j =125°C | 0.50 | | V |
| | | $I_F=15A$ | T _j =25°C | 0.61 | 0.70 | V |
| | | | T _j =125°C | 0.57 | | V |


*Pulse test: pulse width ≤300μs, duty cycles ≤ 2.0%.

Typical Characteristics


Forward Current Derating Curve




Forward Characteristics




Reverse Characteristics



Capacitance Characteristics Per Diode




TO-263-2L Package Outline Dimensions



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|--------|----------------------|-------|
| | Min. | Max. | Min. | Max. |
| A | 4.470 | 4.670 | 0.176 | 0.184 |
| A1 | 0.000 | 0.150 | 0.000 | 0.006 |
| B | 1.120 | 1.420 | 0.044 | 0.056 |
| b | 0.710 | 0.910 | 0.028 | 0.036 |
| b1 | 1.170 | 1.370 | 0.046 | 0.054 |
| c | 0.310 | 0.530 | 0.012 | 0.021 |
| c1 | 1.170 | 1.370 | 0.046 | 0.054 |
| D | 10.010 | 10.310 | 0.394 | 0.406 |
| E | 8.500 | 8.900 | 0.335 | 0.350 |
| e | 2.540 TYP. | | 0.100 TYP. | |
| e1 | 4.980 | 5.180 | 0.196 | 0.204 |
| L | 14.940 | 15.500 | 0.588 | 0.610 |
| L1 | 4.950 | 5.450 | 0.195 | 0.215 |
| L2 | 2.340 | 2.740 | 0.092 | 0.108 |
| L3 | 1.300 | 1.700 | 0.051 | 0.067 |
| Phi | 0° | 8° | 0° | 8° |
| V | 5.600 REF. | | 0.220 REF. | |

TO-263-2L Suggested Pad Layout




Note:

1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.05 mm.
3. The pad layout is for reference purposes only.

TO-263-2L Tape and Reel

TO-263-2L Embossed Carrier Tape




Packaging Description:


TO-263-2L parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 800 units per 13" or 33.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

| Dimensions are in millimeter | | | | | | | | | | |
|------------------------------|-------|-------|------|-------|------|-------|------|-------|------|-------|
| Pkg type | A | B | C | d | E | F | P0 | P | P1 | W |
| TO-263-2L | 10.80 | 16.13 | 5.21 | Ø1.55 | 1.75 | 11.50 | 4.00 | 16.00 | 2.00 | 24.00 |

TO-263-2L Tape Leader and Trailer



TO-263-2L Reel



| Dimensions are in millimeter | | | | | | |
|------------------------------|---------|--------|--------|------|------|--------|
| Reel Option | D | D1 | D2 | W1 | W2 | I |
| 13"Dia | Ø330.00 | 100.00 | Ø21.00 | 24.4 | 30.4 | Ø13.00 |

| REEL | Reel Size | Box | Box Size(mm) | Carton | Carton Size(mm) | G.W.(kg) |
|---------|-----------|---------|--------------|-----------|-----------------|----------|
| 800 pcs | 13 inch | 800 pcs | 340×336×36 | 8,000 pcs | 400×353×365 | |