






PART NUMBER 10046971-052LF




SECTION A-A

NOTE:
1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
2. PACKING SPEC. GS-14-937
3. PRODUCT SPEC. GS-12-338.
4. MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.
5. PART NUMBER 10046971-052LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A
WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.
6. THE PINS 5,6,10,11,15,16,23,24,28,29,33,34 ARE OMITTED.


spec ref	*	dr	Jackie Huang	2015/02/11	projection	MM	size	A2	scale	3:1
tolerance std	ISO 406 ISO 1101	eng	Hai-Ling Liu	2015/04/06	chr	Terris Liu	2015/04/06	ecn no	-	
surface	ISO 1302	appr	Pei-Ming Zheng	2015/04/06	product family		rel level	Released		
linear	0.X ±0.5 0.XX ±0.25 0.XXX ±0.100	title	PEC V/T STB 2x19P 12P OMITTED	cat. no.		Product - Customer Drw	sheet 1 of 2	rev	A	
angular	0° ±2°	www.fci.com								



RECOMMENDED EDGE CARD LAYOUT



RECOMMENDED HOST BOARD LAYOUT

spec ref		*		dr Jackie Huang		2015/02/11		projection		size A2		scale 2:1					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Hai-Ling Liu		2015/04/06		 MM 		ecn no		-					
ISO 406				chr Terris Liu		2015/04/06				rel level		Released					
ISO 1101				appr Pei-Ming Zheng		2015/04/06				product family							
surface 		linear		0.X ±0.5				title		PEC V/T STB		dwg no		10046971-052		rev	
		0.XX ±0.25															
		0.XXX ±0.100															
ISO 1302		angular		0° ±2°		www.fci.com		cat. no.		Product - Customer Drw		sheet 2 of 2		A			