



NTC Thermistors, Radial Leaded and Coated



LINKS TO ADDITIONAL RESOURCES



QUICK REFERENCE DATA		
PARAMETER	VALUE	UNIT
Resistance value at 25 °C	30 to 220K	Ω
Tolerance on R_{25} -value (point matched)	$\pm 1, \pm 2, \pm 3, \pm 5, \pm 10$	%
Temperature accuracy (curve tracking)	$\pm 0.2, \pm 0.5, \pm 1$	°C
$B_{25/75}$ -value	3477 to 3964	K
$B_{25/85}$ -value	3468 to 3974	K
Maximum dissipation	50 to 100	mW
Dissipation factor δ (for information only)	2 to 3.5	mW/K
Thermal time constant τ (for information only)	6 to 14	s
Response time (oil) (for information only)	1.3	s
Operating temperature range at zero power (short term)	-40 to +125 (150)	°C
Weight	≈ 0.075 to 0.15	g

FEATURES

- Small size - conformally coated
- Wide resistance range
- Available in 4 different R-T curves
- Available in point matched tolerances down to 1 % and curve tracking precision down to ± 0.2 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS COMPLIANT

APPLICATIONS

Temperature measurement, sensing and control in industrial, consumer and telecom applications. For on-board sensing or for accurate remote sensing in metal probes or housings.

DESCRIPTION

Models T, M, and C are conformally coated, leaded thermistors. The coating is baked-on phenolic for durability and long-term stability. Models M and C have tinned solid copper leads. Model T has solid nickel wires with Teflon® insulation.

DESIGN-IN SUPPORT

For complete Curve Computation, visit:
www.vishay.com/thermistors/ntc-rt-calculator/

T, M, C PRODUCT DATA AND R_{25} RESISTANCE RANGE AVAILABILITY

CURVE	$B_{25/75}$ (K)	$B_{25/85}$ (K)	TCR_{25} (%/K)	T (kΩ)	M (kΩ)	C (kΩ)	$R_{25} \pm \text{TOL. AVAILABILITY}$
2	3477	3486	-3.84	0.03 to 3.3			1, 2, 3, 5, 10
9	3679	3694	-4.03	10 to 56			1, 2, 3, 5, 10
8	3925	3943	-4.30	20 to 220			1, 2, 3, 5, 10
1	3964	3974	-4.39	0.2 to 18			1, 2, 3, 5, 10
Maximum dissipation at 25 °C in mW				50	75	100	
Dissipation factor in mW/K ⁽¹⁾				2.0	2.5	3.0	
Response time in s ⁽¹⁾				1.3	1.2	1.4	
Thermal time constant in s ⁽¹⁾				14	10	6	

Note

⁽¹⁾ For information only, dissipation factor, response time, and thermal time constant are wire type and product size dependent

STANDARD RESISTANCE VALUES at 25 °C in Ω

33	82	270	680	2.2K	5.6K	18K	50K	150K
39	100	330	820	2.7K	6.8K	22K	56K	220K
47	120	390	1K	3.3K	8.2K	27K	68K	
50	150	470	1.2K	3.9K	10K	33K	82K	
56	180	500	1.5K	4.7K	12K	39K	100K	
68	220	560	1.8K	5.0K	15K	47K	120K	

Note

- Most popular and available values, intermediate resistance values and tolerances available on request



**GLOBAL PART NUMBER AND ORDERING INFORMATION**

Global Part Numbering: 01C2001FP for POINT MATCHED THERMISTORS

0	1	C	2	0	0	1	F	P									
CURVE NR			GLOBAL MODEL			RESISTANCE VAL			POINT MATCH TOLERANCE			PACKAGING					
01 02 08 09			T M C			2001 = 2K 1503 = 150K			F = ± 1 % G = ± 2 % H = ± 3 % J = ± 5 % K = ± 10 %			F = lead (Pb)-free, bulk P = tin / lead, bulk					

Global Part Numbering: 01C2001SPC3 for CURVE TRACKING THERMISTORS

0	1	C	2	0	0	1	S	P	C	3							
CURVE			GLOBAL MODEL			RESISTANCE VALUE		CHARACTERISTICS		PACKAGING		CURVE TRACK TOLERANCE ⁽¹⁾					
01 08 09			T M C			2001 = 2K		S		F = lead (Pb)-free, bulk P = tin / lead, bulk		A3 A4 A5 A8 B3 B4 B5 B8 C3 C5 C8					

Note⁽¹⁾ See following pages for tolerance explanations and details**DIMENSIONS** in inches (millimeters)**TYPE M, C****TYPE T**

PRODUCT TYPE	WIRE GAUGE/DIAMETER ⁽¹⁾
Type M	AWG 30: 0.0100 (0.254)
Type C	AWG 28: 0.0126 (0.320)
Type T	Insulated AWG 30: 0.0100 (0.254)

Note⁽¹⁾ Additional wire gauges (non-insulated) available as AWG24 (type E), AWG26 (type B) and AWG32 (type F). Please contact Vishay (thermistor1@vishay.com) for further details

CURVE NUMBER	R_{25} MIN. Ω	DIAMETER INCH (mm)	STANDARD R_{25} RANGE Ω	DIAMETER INCH (mm)	
		R_{25} MIN.		R_{25} MAX.	R_{25} MIN.
2	30	0.342 (8.69)	330 to 3K	0.095 (2.41)	0.136 (3.45)
9			10K to 56K	0.095 (2.41)	0.150 (3.81)
8	20K	0.131 (3.33)	27K to 220K	0.095 (2.41)	0.125 (3.18)
1	200	0.315 (8.00)	1.8K to 18K	0.095 (2.41)	0.136 (3.45)

Note

- Maximum body diameter is dependent on selected curve number and value, the lower resistance values have the largest diameter. For a specific part number within the given resistance ranges, please contact thermistor1@vishay.com for maximum diameter information



TOLERANCES AVAILABLE FOR TYPE T, M, AND C THERMISTORS

DESCRIPTION OF THERMISTOR TOLERANCES

The many applications of thermistors have mandated the need for two basic tolerance schemes for these products - curve tracking and point match thermistors. An example of the resistance tolerance at various temperatures for the two different tolerancing methods is described in the following graph:




Fig. 1

CURVE TRACKING TOLERANCE

Thermistors are calibrated at the high temperature of the curve track range and then final tested at the low temperature of the curve track range. This ensures that the thermistor will meet the specified temperature accuracy at every temperature within the desired temperature range. Several temperature ranges are available and the accuracy of the thermistor may be $\pm 0.2^\circ\text{C}$, $\pm 0.5^\circ\text{C}$, and $\pm 1.0^\circ\text{C}$. The curve tracking temperature ranges and their code designators are shown in figure 1 and "Standard Electrical Specifications for Curve Tracking Thermistors" table.

To specify, add the appropriate suffix from the following table to the part number.

Example: 01M1002SFB3 = curve 1, 10 k Ω at +25 $^\circ\text{C}$, curve tracking to $\pm 0.5^\circ\text{C}$ from 0 $^\circ\text{C}$ to +70 $^\circ\text{C}$

STANDARD ELECTRICAL SPECIFICATIONS FOR CURVE TRACKING THERMISTORS												
TEMPERATURE RANGE FOR SPECIFIED ACCURACY		0 $^\circ\text{C}$ to +70 $^\circ\text{C}$			0 $^\circ\text{C}$ to +100 $^\circ\text{C}$		25 $^\circ\text{C}$ to +90 $^\circ\text{C}$			0 $^\circ\text{C}$ to +50 $^\circ\text{C}$		
ACCURACY		$\pm 1^\circ\text{C}$	$\pm 0.5^\circ\text{C}$	$\pm 0.2^\circ\text{C}$	$\pm 1^\circ\text{C}$	$\pm 0.5^\circ\text{C}$	$\pm 1^\circ\text{C}$	$\pm 0.5^\circ\text{C}$	$\pm 0.2^\circ\text{C}$	$\pm 1^\circ\text{C}$	$\pm 0.5^\circ\text{C}$	$\pm 0.2^\circ\text{C}$
PART NO. SUFFIX		- A3	- B3	- C3	- A4	- B4	- A5	- B5	- C5	- A8	- B8	- C8
CURVE NUMBER	01	X	X	X	X	X	X	X	X	X	X	X
	08	X	X	X	X	X	X	X	X	X	X	X
	09	X	X	X	X	X	X	X	X	X	X	X



POINT MATCH TOLERANCE

The standard leaded thermistors are calibrated and tested at 25 °C to a tolerance of $\pm 5\%$ or $\pm 10\%$; however, tighter tolerance, point matched thermistors are readily available as are special point match temperatures to fit your application.

Since these thermistors have only one controlled point of reference (the point match temperature), the resistance at other temperatures is given by the specific curve resistance vs. temperature ratio.

POINT MATCH TOLERANCES VS. TEMPERATURE




Fig. 2

Point match resistance tolerances at temperatures other than 25 °C are not the same as at the calibration temperature. This difference is presented in Fig. 2.

The tolerance at any given temperature is the point match tolerance plus a manufacturing tolerance depending on the specific curve.

DESIGN-IN SUPPORT

A spreadsheet is available for the Vishay thermistor part numbers that gives you the resistance vs temperature data, the temperature coefficients and accuracy levels at any given temperature range and step. The Steinhart & Hart formula and coefficients A, B, and C are shown as well. This data can be obtained by visiting the Vishay NTC curve computation page at: www.vishay.com/thermistors/ntc-curve-list/ or send your part number with required temperature range and step to thermistor1@vishay.com.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.