





Copyright FCI.

D



C

B

A



PICK-UP CAP
(OPTIONAL)
SCALE 5:1



spec ref	-	dr	Guo-Min Sun	2015/01/08	projection	MM	size	A3	scale	10:1
tolerance std	ISO 406 ISO 1101	eng	Guo-Min Sun	2015/01/15	chr	-	ecn no	-	rel level	Released
surface	ISO 1302	appr	Tim Yao	2015/01/15	product family	MINITEK	dwg no	10132990	rev	A
linear	0.X ±0.5 0.XX ±0.25 0.XXX ±0.150	angular	0° ±3°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 1 of 2		




PRODUCT NO.	POS	DIM E	DIM F	DIM G	DIM H	PLATING ON CONTACT	PLATING ON TAIL
10132990-001LF	2X2	2.00	4.00	3.90	8.50	0.76um MIN. Au	2.54um MIN. MATTE SN
10132990-002LF	2X3	4.00	6.00	3.90	8.50	0.76um MIN. Au	2.54um MIN. MATTE SN

PRODUCT NUMBER DESCRIPTION:

10132990 - XXX X LF
└───┬───
PACKAGING
TR:TAPE ADN REEL WITH CAP

NOTES:

- 1. MATERIAL HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
UL 94V-0, COLOR BLACK.
- 2. MATERIAL TERMINAL: COPPER ALLOY.
- 3. 0.9Kg MIN. PIN RETENTION IN EITHER DIRECTION.
- 4. PRODUCT SPEC: DPS-12-011
- 5. PACKAGING SPEC: GS-14-436
- 6. DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY. IF
SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.
- 7. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- 8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

spec ref		-		dr	Guo-Min Sun	2015/01/08	projection 	MM 	size	A3	scale	10:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Guo-Min Sun	2015/01/15			ecn no		-	
				chr	-							
				appr	Tim Yao	2015/01/15	product family		MINITEK		rel level Released	
surface ✓ ISO 1302	linear	0.X		±0.5			title 2.00MM UNSHROUDED HEADER SMT, WITH NICKING	dwg no 10132990	rev A			
		0.XX		±0.25								
		0.XXX		±0.150								
angular		0°		±3°		www.fci.com	cat. no.	-	Product - Customer Drw		sheet 2 of 2	