



## SPECIFICATIONS

Rated Current:1.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃


Contact Material:Phosphor Bronze

Contact Plating:Au Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds  
(260℃ for 10 seconds)



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



## Ordering Information



2443 02 XX X N XX S U X0X

No.of  
Pins  
Per Row  
2~50

Insulator Material  
Option  
A=BK-PBT  
C=BK-PA6T  
D=BK-PA46  
E=BK-PA9T  
F=BK-LCP

Contact Plating  
G1:Gold Flash  
G3:2U" Gold  
G4:3U" Gold  
G5:5U" Gold  
G6:10U" Gold  
G7:15U" Gold  
S0:Gold Flash/Tin  
SN:Tin

Packing  
T=Tube  
P=Tube+Cap  
R=Reel+Cap  
M=Reel+Mylar



OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

YiYuSheng

20.04.18

SCALE

UNIT

SIZE

SHEET

PROJ.

FIT

mm

A4

1/1

◆

**JILN**® 深圳市锦凌电子有限公司  
SHENZHEN JINLING ELECTRONIC CO.,LTD

Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

PART NO.

244302XXNXXSUX0X

TITLE:

1.27PF 2xNPin H4.3 180°

A

A