




0055275AY

110 Delta Drive
Pittsburgh, PA 15238
NAFTA Sales: (1)800-245-3984
HK Sales : (852)3102-9337
magnetics@spang.com
www.mag-inc.com



MPP Permeability (μ)	A_L (nH/T ²)	Core Marking			Coating Color
		Lot Number	Part Number	Inductance Grade	
300	128 $\pm$ 8%	N/A	N/A	N/A	Clear

Dimensions	Uncoated		Coated Limits			Packaging Bulk Pack 4 bags/box Box Qty= 8000 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	9.65	0.380	10.11	0.398	max	
ID (B)	4.78	0.188	4.45	0.175	min	
HT (C)	3.18	0.125	3.63	0.143	max	

Electrical Characteristics			Physical Characteristics						
Watt Loss @ 100 kHz, 100mT max(mW/cm³)	DC Bias min (oersteds)		Voltage Breakdown wire to wire min (V _{AC})	Break Strength min (kg)	Window Area W _A (mm²)	Cross Section A _e (mm²)	Path Length L _e (mm)	Volume V _e (mm³)	Weight (g)
1050	80%	50%	600	4.9	15.5	7.52	21.8	164	1.4420
	8.50	17.5							

Winding Information						Temperature Rating	
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: 460°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	11.0	Coating Temp (Continuous up to): 130°C
					HT	5.17	
				Completely Full Window	Max OD	13.4	Notes:
					Max HT	7.44	
0%	13.6	40%	15.9	Surface Area (mm²)			Parylene coated, color appears clear to milky white.
20%	14.7	45%	16.2				
25%	15.0	50%	16.5				
30%	15.3	60%	17.2	Unwound Core		310	
35%	15.6	70%	17.9	40% Winding Factor		410	

Typical DC Bias Performance

