



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0402**

Power Rating: **.063 W**

Resistance Value: **143K Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---


Electrical Characteristics

Power Rating	.063 W
Resistance Value	143K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions





Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±25 ppm/°C

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CPF0402B143KE1

Precision Resistor, Thin Film, 0402, .063 W, 143K ohm, .1 %, ±25 ppm/°C, Solder, 2 Termination, Height .3 mm [.012 in], Neohm CPF





TE Part # 1-2176280-4
CPF 0402 140K 0.1% 25PPM 1K RL



TE Part # 1-2176280-6
CPF 0402 147K 0.1% 25PPM 1K RL

Also in the Series | Neohm CPF



Surface Mount Resistors(5842)

Customers Also Bought



TE Part #6-1625999-4
HSC100 4R0 5%



TE Part #2-2176058-5
RLP73K 3A R10 5% 2K RL



TE Part #7-1879208-3
CPF 0402 10K 0.1% 25PPM 1K RL



TE Part #1981584-1
MICRO USB, TYPE A/B, GRAY



TE Part #826646-2
AMPMODU II R/A HEADER




TE Part #2834010-3
SLIM CONTACT FOR WIRE 20-24AWG




TE Part #1-1879215-4
CPF 0402 5K49 0.1% 25PPM 1K RL



TE Part #1546551-2
2P,STRAIGHT,SIDE ENTRY,3.5MM



TE Part #ANT-DB1-WRT-MHF4
Antenna Dome WiFi6 2.4/5.8GHz 1.13 MHF4



TE Part #1-2176476-5
RA73F 2A 71R5 0.1% 1K RL



Documents

Product Drawings

CPF 0402 143K 0.1% 25PPM 1K RL

English

Datasheets & Catalog Pages

CPF-1016

English