



Connectors > Contacts > Connector Contacts



Contact Type: **Tab**
Contact Mating Area Plating Material: **Tin**
Wire Contact Termination Area Plating Material: **Pre-Tin**
Operating Voltage: **600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
Sealable	Yes

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Mating Tab Width	1.5 mm[.06 in]
Mating Tab Thickness	.5 mm[.02 in]
Contact Orientation	Straight
Contact Type	Tab
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	Without
Contact Base Material	Brass
Contact Current Rating (Max)	8 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

--	--



Carrier Strip Mount Orientation	Side Feed
Wire Insulation Support	With

Dimensions

Compatible Insulation Diameter Range	1.7 – 2.8 mm[.067 – .11 in]
Wire Size	.5 – .8 mm²

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-2381313-1 Power Versa-Lock FH CAP, 1X1 KEY A, GWT	 TE Part # 1-2381608-6 Power Versa-Lock TNL CAP, 2X3 KEY A, GWT	 TE Part # 2-2370523-9 CAP, INLINE, POWER VERSA-LOCK, 3X3 KEY B	 TE Part # 3-2378158-2 Power Versa-Lock CAP, 1X2 KEY C
 TE Part # 3-2378158-3 Power Versa-Lock CAP, 1X3 KEY C	 TE Part # 4-2378158-2 Power Versa-Lock CAP, 1X2 KEY D	 TE Part # 5-2378158-2 Power Versa-Lock CAP, 1X2 KEY E	 TE Part # 6-2378158-2 Power Versa-Lock CAP, 1X2 KEY F
 TE Part # 7-2378158-2 Power Versa-Lock CAP, 1X2 KEY G	 TE Part # 8-2378158-2 Power Versa-Lock CAP, 1X2 KEY H	 TE Part # 9-2378158-2 Power Versa-Lock CAP, 1X2 KEY I	 TE Part # 1-2378158-4 Power Versa-Lock CAP, 1X4 KEY A
 TE Part # 2-2378158-4 Power Versa-Lock CAP, 1X4 KEY B	 TE Part # 234914-1 EXT TOOL FOR POWER DBL LOK TAB	 TE Part # 1-2336231-6 Power Versa-Lock TNL CAP, 2X3 KEY A	 TE Part # 1-2337219-6 Power Versa-Lock CAP, 2X3 KEY A
 TE Part # 1-2345729-1 Power Versa-Lock FH CAP, 1X1 KEY A	 TE Part # 1-2370523-9 CAP, INLINE, POWER VERSA-LOCK, 3x3 KEY A	 TE Part # 1-2378158-2 Power Versa-Lock CAP, 1X2 KEY A	 TE Part # 1-2378158-3 Power Versa-Lock CAP, 1X3 KEY A

Also in the Series | Power Versa-Lock 5.0



Connector Caps & Covers(4)

Connector Contacts(12)

Connector Hardware(5)

Connector Seals & Cavity Plugs(9)

Insertion & Extraction Tools(2)

Rectangular Power Connectors(77)

Customers Also Bought

TE Part #1971777-3
PTL TPA HIGH TEMP 1 x 3 BLACK

TE Part #1376394-1
5MM POWER KEY D/L PLATE GREEN

TE Part #53245-2
TERMINAL,PG SPR SPD 16-14 10

TE Part #4-2378158-2
Power Versa-Lock CAP, 1X2 KEY D

TE Part #4-2378159-2
Power Versa-Lock PLUG, 1X2 KEY D

TE Part #8-2378158-2
Power Versa-Lock CAP, 1X2 KEY H

TE Part #1-2378159-2
Power Versa-Lock PLUG, 1X2 KEY A

TE Part #2325347-2
Power Versa-Lock INTERFACE SEAL, 1X2

TE Part #2329914-1
Power Versa-Lock SEAL RECPT, 18-20 AWG

TE Part #2334614-2
Power Versa-Lock BACK COVER 2P

Documents



Product Drawings

Power Versa-Lock SEAL TAB, 18-20 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2329908-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2329908-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2329908-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

VDE Certificate

English