

50KEBS6AFPDHM

✓ ACTIVE


TE Internal #: 3-1609965-9

50A Current Rating, Threaded Bolt Input, Threaded Bolt Output, DELTA (3 wire + ground), Operating Voltage 440 VAC, DIN Rail, 3-Phase Filters

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters



Current Rating: 50 A

Input Termination Type: Threaded Bolt

Output Termination Type: Threaded Bolt

Wiring Configuration: DELTA (3 wire + ground)

Operating Voltage: 440 VAC

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Threaded Bolt
Output Termination Type	Threaded Bolt

Configuration Features

Wiring Configuration	DELTA (3 wire + ground)
----------------------	-------------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	5
Current Rating	50 A
Operating Voltage	440 VAC

Mechanical Attachment

Product Mount Type	DIN Rail
--------------------	----------

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #2-644488-6
06P MTA100 SHRD HDR F/L R/A SN

TE Part #535090-4
096 EURO TYPE C RECEPT ST ASSY

TE Part #6-1393252-1
W67-X2Q12-30=M6/M7/M9/W6/W7

TE Part #7-1625890-0
2W SM M/OX 5% 82K

TE Part #5-1437595-2
TRD11F10WL=SUB MINI ROCKER BLA

TE Part #1-1393767-5
R10-E2X2-V700=R10

TE Part #1-1393766-9
R10-E1X4-24V=R10

Documents

Product Drawings

KEB 50A 1S NUT DELTA 440VAC

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1609965-9_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1609965-9_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_3-1609965-9_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Catalogue - Corcom 3-Phase-Emi-Filter

English

KEB SERIES

English