




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing


DIM.S SHELL	A	B	C	D	Pitch
15	30.84	24.99	16.92	19.28	2.29
26	39.24	33.32	24.70	27.51	2.29
44	53.04	47.04	38.96	41.30	2.29
62	69.32	63.50	55.42	57.71	2.41


REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1			08/29/08	

D-SUB TECHNICAL DATA

SHELL : Steel, 2.5um (100u") min tin over 1.25um (50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
ELECTRICAL : Voltage rating : 500 V RMS at 50 Hz
Insulation resistance >5000 M Ohms
CLIMATIC : Temperature range -55 °C up to 125°C
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE		Amphenol®	
U.S.		DRAWN		Christina.cui 08/29/08			
METRIC		CHECKED		Wk.wang 08/29/08			
		CHECKED					
.X +/-		0.50		TITLE		stamped and formed connector, HR series	
.XX +/-		0.30					
.XXX +/-		0.20					
FRACTIONS +/-							
ANGLES +/-		2°		DRAWING FILE :			
FOR MATERIALS AND FINISHES SEE NOTES				ANGLE OF PROJECTION			
REMOVE SHARP EDGES							
DIMENSIONS							
U.S.		INCHES		SIZE		DRAWING NO.	
METRIC		MM		A4		C L777HRXXXP	
				SCALE		NONE	
				SHEET 1		OF 1	
						REV.	
						1	