

PROTECTION PRODUCTS

Description

PowerClamp TVS diodes are designed for use in harsh transient environments to protect sensitive electronics from damage or latch-up due to EOS, lightning, CDE, and ESD. They feature large cross-sectional area junctions for conducting high transient currents. These devices offer desirable characteristics for board level protection including fast response time, low operating and clamping voltage, and no device degradation.

They feature extremely good protection characteristics highlighted by high surge current capability (80A, $t_p = 8/20\mu s$), low peak ESD clamping voltage, and high ESD withstand voltage (+/- 30kV per IEC 61000-4-2). Each device will protect one data or power line operating at 10V.

P Clamp1021P is in a 2-pin DFN1610N2 package measuring 1.6 x 1.0 mm with a nominal height of 0.50mm. The leads are finished with lead-free NiPdAu. High surge current capability and low clamping voltage making them ideal for protecting VBus, battery, and other power lines in portable electronics, industrial, and consumer electronics applications.

Features

- Transient Protection to
 - ♦ IEC 61000-4-2 (ESD) 30kV (Air), 30kV (Contact)
 - ♦ IEC 61000-4-4 (EFT) 4kV (5/50ns)
 - ♦ IEC 61000-4-5 (Lightning) 80A (8/20 μs)
- Protects one data or power line
- Working Voltage: 10V
- Low leakage current
- Solid-state silicon-avalanche technology


Mechanical Characteristics

- DFN1610N2 package
- Pb-Free, Halogen Free, RoHS/WEEE compliant
- Nominal Dimensions: 1.6 x 1.0 x 0.50 mm
- Lead Finish: NiPdAu
- Marking: Marking code
- Packaging: Tape and Reel


Applications

- Cellular Handsets & Accessories
- Voltage Supply Lines
- Battery protection
- USB VBus
- VBAT

Package Dimension



Schematic & Pin Configuration



Absolute Maximum Ratings

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 8/20\mu s$)	P_{PK}	1680	W
Peak Pulse Current ($t_p = 8/20\mu s$)	I_{PP}	80	A
ESD per IEC 61000-4-2 (Contact) ⁽¹⁾ ESD per IEC 61000-4-2 (Air) ⁽¹⁾	V_{ESD}	± 30 ± 30	kV
Operating Temperature	T_{OP}	-40 to +125	°C
Storage Temperature	T_{STG}	-55 to +150	°C

Electrical Characteristics ($T=25^\circ C$ unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-Off Voltage	V_{RWM}	-40°C to 125°C, Pin 1 to Pin 2			10	V
Reverse Breakdown Voltage	V_{BR}	$I_t = 1\text{ mA}$, Pin 1 to Pin 2	11	12	13	V
Reverse Leakage Current	I_R	$V_{RWM} = 10\text{ V}$, Pin 1 to Pin 2		<10	100	nA
Clamping Voltage	V_C	$I_{PP} = 40\text{ A}$, $t_p = 8/20\mu s$, Pin 1 to Pin 2		16	18	V
		$I_{PP} = 80\text{ A}$, $t_p = 8/20\mu s$, Pin 1 to Pin 2		19	21	
Clamping Voltage ⁽²⁾	V_C	$I_{PP} = 4\text{ A}$, $t_p = 0.2/100\text{ ns}$, Pin 1 to Pin 2		12.7		V
		$I_{PP} = 16\text{ A}$, $t_p = 0.2/100\text{ ns}$, Pin 1 to Pin 2		13.2		
Dynamic Resistance ^{(2), (3)}	R_{DYN}	$t_p = 0.2/100\text{ ns}$ (TLP)		0.04		Ω
Junction Capacitance	C_J	$V_R = 0\text{ V}$, $f = 1\text{ MHz}$		512	600	pF

Notes:


(1): ESD Gun return path to Ground Reference Plane (GRP)

(2): Transmission Line Pulse Test (TLP) Settings: $t_p = 100\text{ ns}$, $t_r = 0.2\text{ ns}$, I_{TLP} and V_{TLP} averaging window: $t_1 = 70\text{ ns}$ to $t_2 = 90\text{ ns}$


(3): Dynamic resistance calculated from $I_{TLP} = 4\text{ A}$ to $I_{TLP} = 16\text{ A}$

Typical Characteristics


Non-Repetitive Peak Pulse Power vs. Pulse Time




Power Derating Curve vs. Temperature




Clamping Voltage vs. Peak Pulse Current ($t_p=8/20\mu$ s)




Forward Voltage vs. Peak Pulse Current ($t_p=8/20\mu$ s)



TLP Characteristic (Positive)




TLP Characteristic (Negative)




Typical Characteristics


ESD Clamping (8kV Contact per IEC 61000-4-2)




ESD Clamping (-8kV Contact per IEC 61000-4-2)




ESD Clamping (30kV Contact per IEC 61000-4-2)



ESD Clamping (-30kV Contact per IEC 61000-4-2)




Outline Drawing - DFN1610N2




- NOTES:
1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
 2. ASSEMBLY SITE DEPENDENT FEATURES

Land Pattern - DFN1610N2



- NOTES:
1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
 2. THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY.
CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR
COMPANY'S MANUFACTURING GUIDELINES ARE MET.


Marking Example



Notes:


- 1) Bar indicates Pin 1 location
- 2) Marking includes line matrix date code

Tape and Reel Specification



SECTION A-A

NOTES: 1.) ALL DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.



PIN 1 Location
(Towards Sprocket Holes)

Ordering Information

Part Number	Qty per Reel	Reel Size
P Clamp1021P.TNT	10,000	7"



Important Notice

Information relating to this product and the application or design described herein is believed to be reliable, however such information is provided as a guide only and Semtech assumes no liability for any errors in this document, or for the application or design described herein. Semtech reserves the right to make changes to the product or this document at any time without notice. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. Semtech warrants performance of its products to the specifications applicable at the time of sale, and all sales are made in accordance with Semtech's standard terms and conditions of sale.

SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS, OR IN NUCLEAR APPLICATIONS IN WHICH THE FAILURE COULD BE REASONABLY EXPECTED TO RESULT IN PERSONAL INJURY, LOSS OF LIFE OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.

The Semtech name and logo are registered trademarks of the Semtech Corporation. All other trademarks and trade names mentioned may be marks and names of Semtech or their respective companies. Semtech reserves the right to make changes to, or discontinue any products described in this document without further notice. Semtech makes no warranty, representation or guarantee, express or implied, regarding the suitability of its products for any particular purpose. All rights reserved.

© Semtech 2019

Contact Information

Semtech Corporation
200 Flynn Road, Camarillo, CA 93012
Phone: (805) 498-2111, Fax: (805) 498-3804
www.semtech.com