
PART NUMBER**25S10PC**

**Rochester Electronics
Manufactured Components**

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All re-creations are done with the approval of the Original Component Manufacturer. (OCM)

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-38535
 - Class Q Military
 - Class V Space Level

Qualified Suppliers List of Distributors (QSLD)

- Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OCM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

REVISIONS

LTR	DESCRIPTION	DATE (YR-MO-DA)	APPROVED
A	NOR 5962-R149-93. Revisions to paragraphs 4.2a(1) and 4.3.2b(1). --tvn	93-04-30	Monica L. Poelking
B	Update to reflect latest changes in format and requirements. Editorial changes throughout. --les	02-06-26	Raymond Monnin
C	Update drawing to current requirements. Editorial changes throughout. - gap	09-07-20	Charles F. Saffle
D	Update drawing to current MIL-PRF-38535 requirements. - rdc	17-11-22	Charles F. Saffle
E	Update drawing to latest MIL-PRF-38535 requirements. - jt	22-08-17	James R. Eschmeyer



Current CAGE code is 67268

THE ORIGINAL FIRST SHEET OF THIS DRAWING HAS BEEN REPLACED.

Revision Status of Sheets

REV																						
SHEET																						
REV	E	E	E	E	E	E	E	E	E	E	E											
SHEET	1	2	3	4	5	6	7	8	9	10	11											

PMIC N/A

**STANDARD
MICROCIRCUIT
DRAWING**

THIS DRAWING IS AVAILABLE
FOR USE BY ALL DEPARTMENTS
AND AGENCIES OF THE
DEPARTMENT OF DEFENSE

PREPARED BY
David W. Queenan

CHECKED BY
D. A. DiCenzo

APPROVED BY
N. A. Hauch

DRAWING APPROVAL DATE
86-12-19

**DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990**
<https://www.dla.mil/LandandMaritime>

**MICROCIRCUIT, DIGITAL, BIPOLAR, FOUR-BIT
SHIFTER, MONOLITHIC SILICON**

AMSC N/A

REVISION LEVEL
E

SIZE
A

CAGE CODE
14933


5962-86718

SHEET 1 OF 11

1. SCOPE

1.1 Scope. This drawing describes device requirements for MIL-STD-883 compliant, non-JAN class level B microcircuits in accordance with MIL-PRF-38535, appendix A.

1.2 Part or Identifying Number (PIN). The complete PIN is as shown in the following example:



1.2.1 Device type. The device type identify the circuit function as follows:

<u>Device type</u>	<u>Generic number</u>	<u>Circuit function</u>
01	25S10	Four-bit shift register with three-state outputs

1.2.2 Case outlines. The case outlines are as designated in MIL-STD-1835 and as follows:

<u>Outline letter</u>	<u>Descriptive designator</u>	<u>Terminals</u>	<u>Package style</u>
E	GDIP1-T16 or CDIP2-T16	16	Dual-in-line package
F	GDFP2-F16 or CDFP3-F16	16	Flat package
2	CQCC1-N20	20	Square chip carrier

1.2.3 Lead finish. The lead finish is as specified in MIL-PRF-38535, appendix A.

1.3 Absolute maximum ratings.

Supply voltage	-0.5 V dc to +7.0 V dc
Input voltage range	-1.5 V dc to +7.0 V dc
Storage temperature range	-65°C to +150°C
Maximum power dissipation (P_D) ^{1/}	1.02 W
Lead temperature (soldering, 10 seconds)	+300°C
Thermal resistance, junction-to-case (θ_{JC})	See MIL-STD-1835
Junction temperature (T_J)	+150°C
DC output current into outputs	30 mA
DC input current	-30 mA to +5.0 mA

1.4 Recommended operating conditions.

Supply voltage range (V_{CC})	+4.5 V dc to +5.5 V dc
Minimum high level input voltage (V_{IH})	2.0 V dc
Maximum low level input voltage (V_{IL})	0.8 V dc
Ambient operating temperature (T_A)	-55°C to +125°C

^{1/} Must withstand the added P_D due to short circuit test (e.g. Ios).

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **2**

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.

MIL-STD-1835 - Interface Standard Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.

MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at <https://quicksearch.dla.mil/>.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **3**

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.

3.2.1 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 1.

3.2.3 Truth table. The truth table shall be as specified on figure 2.

3.2.4 Logic diagram. The logic diagram shall be as specified on figure 3.

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full ambient operating temperature range.

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.

3.5 Marking. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked. For packages where marking of the entire SMD PIN number is not feasible due to space limitations, the manufacturer has the option of not marking the "5962-" on the device.

3.5.1 Certification/compliance mark. A compliance indicator "C" shall be marked on all non-JAN devices built in compliance to MIL-PRF-38535, appendix A. The compliance indicator "C" shall be replaced with a "Q" or "QML" certification mark in accordance with MIL-PRF-38535 to identify when the QML flow option is used.

3.6 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DLA Land and Maritime-VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.

3.7 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.

3.8 Notification of change. Notification of change to DLA Land and Maritime-VA shall be required for any change that affects this drawing.

3.9 Verification and review. DLA Land and Maritime, DLA Land and Maritime's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

STANDARD MICROCIRCUIT DRAWING DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990	SIZE A		5962-86718
		REVISION LEVEL E	SHEET 4

TABLE I. Electrical performance characteristics.

Test	Symbol	Conditions -55°C ≤ T _A ≤ +125°C unless otherwise specified		Group A subgroups	Device type	Limits		Unit
						Min	Max	
High level output voltage	V _{OH}	V _{CC} = 4.5 V, I _{OH} = -1.0 mA, V _{IN} = 0.7 V or 2.0 V		1, 2, 3	01	2.4		V
Low level output voltage at Q outputs	V _{OL}	V _{CC} = 4.5 V, I _{OL} = 12 mA, V _{IN} = 2.0 V or 0.7 V		1, 2, 3	01		0.5	V
Input clamp voltage	V _{IC}	V _{CC} = 4.5 V, I _{IH} = -18 mA		1, 2, 3	01		-1.5	V
Low level input current	I _{IL}	V _{CC} = 5.5 V V _{IN} = 0.5	I ₃ , I-3, S ₀ , S ₁ , — OE	1, 2, 3	01		-2.0	mA
			All other inputs	1, 2, 3	01		-3.0	mA
High level input current	I _{IH1}	V _{CC} = 5.5 V, V _{IN} = 2.7 V	I ₃ , I-3, S ₀ , S ₁ , — OE	1, 2, 3	01		50	μA
			All other inputs	1, 2, 3	01		75	μA
	I _{IH2}	V _{CC} = 5.5 V, V _{IN} = 5.5 V	1, 2, 3	01		1.0	mA	
Short circuit output current	I _{OS}	V _{CC} = 5.5 V,		1, 2, 3	01	-40	-100	mA
Supply current	I _{CC}	V _{CC} = 5.5 V, all outputs open, all inputs = GND		1, 2, 3	01		85	mA
Off-state output current	I _{OZH}	V _{CC} = 5.5 V, V _{OUT} = 2.4 V		1, 2, 3	01		50	μA
	I _{OZL}	V _{CC} = 5.5 V, V _{OUT} = 0.5 V		1, 2, 3	01		-50	μA
Functional test		See 4.3.1c		7, 8				
Propagation delay time, data to output Y	t _{PLH1}	C _L = 15 pF ±10%, R _L = 280 Ω ±5%	<u>2</u> /	9	01		7.5	ns
			<u>3</u> /	9, 10, 11	01		10	ns
	t _{PHL1}		<u>2</u> /	9	01		12	ns
			<u>3</u> /	9, 10, 11	01		16	ns

See footnotes at end of table.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **5**

TABLE I. Electrical performance characteristics - Continued.

Test	Symbol	Conditions -55°C ≤ T _A ≤ +125°C unless otherwise specified		Group A subgroups	Device type	Limits		Unit
						Min	Max	
Propagation delay time, from select to output Y	t _{PLH2}	C _L = 15 pF ± 10%, R _L = 280 Ω ± 5%	<u>2/</u>	9	01		17	ns
			<u>3/</u>	9, 10, 11	01		22	ns
	t _{PHL2}		<u>2/</u>	9	01		20	ns
			<u>3/</u>	9, 10, 11	01		26	ns
Propagation delay time, from OE to output Y	t _{PZH}		<u>2/</u>	9	01		19.5	ns
			<u>3/</u>	9, 10, 11	01		25	ns
	t _{PZL}		<u>2/</u>	9	01		21	ns
			<u>3/</u>	9, 10, 11	01		27	ns
Propagation delay time, from $\overline{\text{OE}}$ to output Y	t _{PHZ}		<u>2/</u>	9	01		8	ns
			<u>3/</u>	9, 10,11	01		10	ns
	t _{PLZ}		<u>2/</u>	9	01		15	ns
			<u>3/</u>	9, 10, 11	01		20	ns

1/ Not more than one output should be shorted at a time and the duration of the short circuit condition should not exceed one second.

2/ V_{CC} = 5.0 V.

3/ V_{CC} = 4.5 V to 5.5 V.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **6**

Device type 01		
Case outlines	E and F	2
Terminal number	Terminal symbols	
1	I ₋₃	NC
2	I ₋₂	I ₋₃
3	I ₋₁	I ₋₂
4	I ₀	I ₋₁
5	I ₁	I ₀
6	I ₂	NC
7	I ₃	I ₁
8	GND	I ₂
9	S ₁	I ₃
10	S ₀	GND
11	Y ₃	NC
12	Y ₂	S ₁
13	$\overline{\text{OE}}$	S ₀
14	Y ₁	Y ₃
15	Y ₀	Y ₂
16	V _{CC}	NC
17	---	$\overline{\text{OE}}$
18	---	Y ₁
19	---	Y ₀
20	---	V _{CC}

FIGURE 1. Terminal connections.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

5962-86718

REVISION LEVEL
E

SHEET **7**

\overline{OE}	S ₁	S ₀	I ₃	I ₂	I ₁	I ₀	I ₋₁	I ₋₂	I ₋₃	Y ₃	Y ₂	Y ₁	Y ₀
H	X	X	X	X	X	X	X	X	X	Z	Z	Z	Z
L	L	L	D ₃	D ₂	D ₁	D ₀	X	X	X	D ₃	D ₂	D ₁	D ₀
L	L	H	X	D ₂	D ₁	D ₀	D ₋₁	X	X	D ₂	D ₁	D ₀	D ₋₁
L	H	L	X	X	D ₁	D ₀	D ₋₁	D ₋₂	X	D ₁	D ₀	D ₋₁	D ₋₂
L	H	H	X	X	X	D ₀	D ₋₁	D ₋₂	D ₋₃	D ₀	D ₋₁	D ₋₂	D ₋₃

H = High level

L = Low level

X = Don't care

Z = High impedance state

D_n at input I_n may be either high or low and output Y_m will follow the selected D_n input level.

FIGURE 2. Truth table.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **8**




FIGURE 3 Logic diagram.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **9**

4. VERIFICATION

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.

4.2 Screening. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:

- a. Burn-in test, method 1015 of MIL-STD-883.
 - (1) Test condition A, C, or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
- b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	---
Final electrical test parameters (method 5004)	1*, 2, 3, 7, 8, 9
Group A test requirements (method 5005)	1, 2, 3, 7, 8, 9, 10**, 11**
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3

* PDA applies to subgroup 1.

** Subgroups 10 and 11, if not tested, shall be guaranteed to the specified limits in table I.

4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.

4.3.1 Group A inspection.

- a. Tests shall be as specified in table II herein.
- b. Subgroups 4, 5, and 6 in table I, method 5005 of MIL-STD-883 shall be omitted.
- c. Subgroups 7 and 8 shall include verification of the truth table.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
E

5962-86718

SHEET **10**

4.3.2 Groups C and D inspections.

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition A, C, or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal, or email communication.

6.4 Record of users. Military and industrial users shall inform DLA Land and Maritime when a system application requires configuration control and the applicable SMD to that system. DLA Land and Maritime will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DLA Land and Maritime-VA, telephone (614) 692-8108.

6.5 Comments. Comments on this drawing should be directed to DLA Land and Maritime-VA, Columbus, Ohio 43218-3990, or telephone (614) 692-0591.

6.6 Approved sources of supply for device class M. Approved sources of supply for class M are listed in MIL-HDBK-103. The vendors listed in MIL-HDBK-103 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DLA Land and Maritime -VA.

STANDARD MICROCIRCUIT DRAWING DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990	SIZE A		5962-86718
		REVISION LEVEL E	SHEET 11

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 22-08-17

Approved sources of supply for SMD 5962-86718 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML-38535 during the next revision. MIL-HDBK-103 and QML-38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DLA Land and Maritime-VA. This information bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML-38535. DLA Land and Maritime maintains an online database of all current sources of supply at <https://landandmaritimeapps.dla.mil/programs/smcr/>.

Standard microcircuit drawing PIN <u>1</u> /	Vendor CAGE number	Vendor similar PIN <u>2</u> /
5962-8671801EA	3V146	25S10/BEA
	<u>3</u> /	GEM08301B2A
	<u>3</u> /	AM25S10/BEA
5962-8671801EC	<u>3</u> /	GEM08301BEC
5962-8671801FA	3V146	25S10/BFA
	<u>3</u> /	GEM08301BFA
	<u>3</u> /	AM25S10/BFA
5962-8671801FC	<u>3</u> /	GEM08301BFC
5962-86718012A	3V146	25S10/B2A
	<u>3</u> /	GEM08301B2A
	<u>3</u> /	AM25S10/B2A
5962-86718012C	<u>3</u> /	GEM08301B2C

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the vendor to determine its availability.
- 2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.
- 3/ Not available from an approved source of supply.

Vendor CAGE
number

3V146

Vendor name
and address

Rochester Electronics Inc.
16 Malcolm Hoyt Drive
Newburyport, MA 01950

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.