



Relays & Contactors > Electromechanical Relays > Signal Relay with Dielectric Strength



Relay & Contactor Type: **General Purpose Signal Relay**

Coil Magnetic System: **Monostable, Polarized**

Contact Arrangement: **2 Form C DPDT-CO**

Current Type: **DC**

Contact Current Rating: **2 A**

[All Signal Relay with Dielectric Strength \(3\)](#)

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay
------------------------	------------------------------

Configuration Features

Contact Special Features	Bifurcated/Twin Contacts
Contact Number of Poles	2
Coil Special Features	Overmolded Coil
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	1500 Vrms
Contact Limiting Making Current	2 A
Contact Limiting Short-Time Current	2 A
Contact Limiting Continuous Current	2 A
Contact Switching Voltage (Max)	220 VDC



Contact Switching Load (Min)	10mA @ .2V
Voltage Standing Wave Ration (HF Parameter)	1.04 @ 100MHz, 1.4dB @ 900MHz
Insulation Initial Dielectric Between Adjacent Contacts	1000 Vrms
Insulation Initial Resistance	1000 MΩ
Contact Limiting Breaking Current	2 A
Coil Resistance	720 Ω
Contact Current Rating	2 A
Coil Voltage Rating	12 VDC
Contact Voltage Rating	220 VDC
Coil Power Rating DC	.2 W
Insulation Initial Dielectric Between Contacts & Coil	1500 Vrms

Signal Characteristics

Isolation (HF Parameter)	-20.7dB @ 900MHz, -39dB @ 100MHz
Insertion Loss (HF Parameter)	-.02dB @ 100MHz, -.27dB @ 900MHz

Body Features

Product Weight	2.8 g[.0988 oz]
Enclosure Type	Flux Resistant Automatic Soldering

Contact Features

Contact Material	AgNi
Contact Plating Material	Gold

Termination Features

Main Termination & Connection Type	PCB SMT
Coil Termination & Connection Type	PCB SMT

Mechanical Attachment

Product Mount Type	Printed Circuit Board
--------------------	-----------------------

Dimensions

Insulation Clearance Between Contact & Coil	1.3 mm[.051 in]
Insulation Creepage Between Contact & Coil	2.5 mm[.098 in]
Product Width	7.2 mm[.283 in]
Product Length	14.6 mm[.574 in]
Product Height	9.9 mm[.389 in]

Usage Conditions



Environmental Category of Protection	RTIII
Operating Temperature Range	-40 – 85 °C
Environmental Ambient Temperature (Max)	85 °C[185 °F]

Operation/Application

Performance Type	High Dielectric
Solder Process	Reflow Solder
Coil Magnetic System	Monostable, Polarized
Current Type	DC

Packaging Features

Packaging Method	Reel
------------------	------

Other

Environmental Ambient Temperature Class	70 – 85 °C
Coil Power Rating Class	.15 – .2 W
Contact Current Class	0 – 2 A
Height Class (Mechanical)	9 – 10 mm
Length Class (Mechanical)	14 – 16 mm
Width Class (Mechanical)	6 – 8 mm

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1422025-7
V23079A2003X074

TE Part # 1422006-3
V23079G2006X073

Also in the Series | Axicom P2 Signal Relay

Electromechanical Relays(44)

Customers Also Bought

TE Part #5-5179009-3
0.8FH,R09H.5,080,08/Sn,TU

TE Part #1735446-3
2MM PITCH HPI POST HEADER,
VERTICAL, 3P

TE Part #84984-8
1mm FFC DIP V ASSY 8P NAT(TB)

TE Part #6-1437624-7
PKG70B1/4=KNOB PLASTIC BLK LEX




TE Part #2-36150-1
TERM, RING, PIDG, 22-16, 6, T&R




TE Part #80803-000
LS809-31 Liquid Level Sensor



TE Part #3-1768018-5
EET-1113P-9



TE Part #284166-E
STVB 64 F AB VV 7-00 TL 4,0 * 247
E007 1



TE Part #284308-E
STVC 96 F ABC VV 7-00 TL 4,0 * 247
E007

Documents

Product Drawings

V23079G2003X074

English

CAD Files

Customer View Model

ENG_CVM_CVM_1393789-3_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393789-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393789-3_A.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1422006-4_D1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1422006-4_D1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1422006-4_D1.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Axicom Signal and High Frequency Relays (RF Switches) APPLICATION NOTE #2

English

Transportation, Storage, Handling, Assembly and Testing of AXICOM SMT Relays

English

P2 Relay Datasheet

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English