



Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Bushing Thread Size: **1/4-40 UNS-2A**

Contact Base Material: **Copper**

Switch Contact Plating Material: **Silver**

Process Sealed: **No**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Sealed Device	Yes
Toggle Style	Flat
Switch Type	Toggle

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	(On) Off (On)

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	1000 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Contact Current Rating	5 A
Operating Voltage	28 VDC

Body Features



Actuator Finish	Nickel
Bushing Thread Size	1/4-40 UNS-2A
Product Orientation	Vertical
Bushing Style	Threaded

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver

Mechanical Attachment

Product Mount Type	Panel
--------------------	-------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	11.43 mm[.45 in]
---------------	------------------

Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-1825136-5
A101SYCQ04



TE Part # 1825136-7
A101KZQ04



TE Part # 4-1825136-9
A101SYZQ04



TE Part # 5-1825136-9
A108P3ZQ04



TE Part # 4-1825136-3
A101SYAQ04

Also in the Series | Alcoswitch Gemini A



Toggle Switches(77)

Customers Also Bought






TE Part #165565-1
2,8 PIDG FASTON REC



TE Part #1-480318-0
02P CMNL PLUG HSG F/H NATL



TE Part #8-1437627-7
G13A=BUTTON GUARD ALUM



TE Part #60618-6
CMNL PIN AUPHBZ L/P



TE Part #3-1825139-2
A211P3ZQ04

Documents

Product Drawings

A105P3ZQ04

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1825137-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1825137-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1825137-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

English