

TO-5/.100 GRID

TE CONNECTIVITY (TE)

JMGSCDD-5MW = M39016/43-049M

2-1617150-8

TE Internal Number: 2-1617150-8

Mil-Spec: **M39016/43-049M**

Alias ID: JMGSCDD-5MW

Not EU RoHS or ELV Compliant

[Find Compliant Alternatives](#)Contact Arrangement **2 Form C, DPDT, 2 C/O**Input Voltage (VDC) **2.9**Coil Suppression Diode **With**MOSFET Driver **Without**Transistor Driver **Without** Active

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information. Product Type Features

MOSFET Driver

Without

Coil Latching

Without

Enclosure Type

Hermetically Sealed

Product Type

Relay

Relay Type

Military/Aerospace High Performance

Configuration Features

Transistor Driver

Without

Electrical Characteristics

Input Voltage (VDC)

2.9

Coil Suppression Diode

With

Coil Voltage (VDC)

5Coil Resistance (Ω)**64**

Coil Power Rating (DC) (mW)

391

Coil Polarity Protection Diode

With

Contact Switching Voltage (Max)

28

Actuating System

DC

Vibration

30G's, 10 – 3000Hz

Coil Power Measurement

Milliwatts

Coil Magnetic System

Non-Polarized, Monostable

Shock

75G's, 6ms

Contact Features

Contact Arrangement

2 Form C, DPDT, 2 C/O

Contact Current Rating (A)

1

Pin Configuration

.175" Diameter Mounting Pad

Contact Current Class

Low Level – 1 A

Termination Features

Termination Type

PC Pins

Mechanical Attachment

Mounting Type

PC Board

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

