




VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
W0801120-2PW2431	2	0.80	3.85
W0801120-3PW2431	3	1.60	4.65
W0801120-4PW2431	4	2.40	5.45
W0801120-5PW2431	5	3.20	6.25
W0801120-6PW2431	6	4.00	7.05
W0801120-7PW2431	7	4.80	7.85
.....			
W0801120-24PW2431	24	18.40	21.45

- NOTES:
- 1.BASE: LCP
 - 2.PIN: Brass
 - 3.Solder Tab: Brass
- SPECIFICATIONS:
- 1.Spacing: 0.8
 - 2.Voltage Rating: 30V AC DC
 - 3.Current Rating: 0.5A AC DC
 - 4.Insulation Resistance: 100MΩ Min
 - 5.Contact Resistance: 20mΩ Max
 - 6.Withstanding voltage: 200V AC 1/Minute
 - 7.Temperatuer Range: -25℃ ~+ 85℃

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. W0801120-XPW2431	TITLE: WAFER 0.8 卧贴		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1