




RoHs


VER	MARK	PR. BY	DESCRIPTION	DATE

技术要求:


1. 塑件材料 :PA66 (UL-94V-0)
2. 接触件 :黄铜镀锡
3. 接触电阻 :≤10mΩ
4. 绝缘电阻 :≥100MΩ
5. 额定电压 :250V AC DC
6. 额定电流 :2.0A AC DC
7. 耐压 :能承受 1000V AC/Minute
8. 工作温度 : -25° ~ +85°
9. 可焊性试验 :浸锡面积 ≥95% 温度 235⁺⁵₋₀, 时间 2.5±0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

PIN number variable size comparison table

PART NO	PIN	A	B
W2001100-2PW2113	2	2.00	6.00
W2001100-3PW2113	3	4.00	8.00
W2001100-4PW2113	4	6.00	10.00
W2001100-5PW2113	5	8.00	12.00
W2001100-6PW2113	6	10.00	14.00
W2001100-7PW2113	7	12.00	16.00
.....			
W2001100-20PW2113	20	38.00	42.00



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



2	端子 Contact	黄铜	N*1	电镀(锡):整个 表面镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO. W2001100-XPW2113	TITLE: PH2.0MM 弯针
.XX ±0.20	X.X° ±1°	DESIGN: James	CUSTOMER
.XXX ±0.10	X.XX° ±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	SCALE N:A
			UNITS MM
			SHEET 1/1