





RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table				
Part No	Pin	A	B	C
W100110-2PY113	2	1.00	5.00	2.40
W100110-3PY113	3	2.00	6.00	3.40
W100110-4PY113	4	3.00	7.00	4.40
W100110-5PY113	5	4.00	8.00	5.40
W100110-6PY113	6	5.00	9.00	6.40
W100110-7PY113	7	6.00	10.00	7.40
W100110-8PY113	8	7.00	11.00	8.40
W100110-9PY113	9	8.00	12.00	9.40
W100110-10PY113	10	9.00	13.00	10.40
W100110-11PY113	11	10.00	14.00	11.40
W100110-12PY113	12	11.00	15.00	12.40
W100110-13PY113	13	12.00	16.00	13.40
W100110-14PY113	14	13.00	17.00	14.40
W100110-15PY113	15	14.00	18.00	15.40
W100110-16PY113	16	15.00	19.00	16.40
W100110-17PY113	17	16.00	20.00	17.40
W100110-18PY113	18	17.00	21.00	18.40
W100110-19PY113	19	18.00	22.00	19.40
W100110-20PY113	20	19.00	23.00	20.40

技术要求Specification:
1、材质Material: PA66 UL94V-0;
2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.* ±5°	PART NO. W100110-XPY113	TITLE: SH1.0MM HOUSING
.XX ±0.20	X.X* ±1°		
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	
			SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1