




VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
W254110K-2PW2113	2	2.50	7.50
W254110K-3PW2113	3	5.00	10.00
W254110K-4PW2113	4	7.50	12.50
W254110K-5PW2113	5	10.00	15.00
W254110K-6PW2113	6	12.50	17.50
.....			
W254110K-20PW2113	20	47.50	52.50

- 技术要求：
1. 塑件材料：PA66 (UL-94V-0)
 2. 接触件：黄铜镀锡
 3. 接触电阻： $\leq 10m\Omega$
 4. 绝缘电阻： $\geq 100m\Omega$
 5. 额定电压：250V AC DC
 6. 额定电流：2.0A AC DC
 7. 耐压：能承受 1000V AC/Minute
 8. 工作温度： $-25^{\circ}\sim +85^{\circ}$
 9. 可焊性试验：浸锡面积 $\geq 95\%$ 温度 235° ，时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求。

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u~MIN, 再镀 锡 80u~MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	W254110K-XPW2113	HA2.54MM 带扣 弯针
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	
			SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1