



SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Phosphor Bronze




Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Max.Processing Temp:

(PBT)245℃±5℃ For 5~10 Second

(PA6T/LCP/PA9T)260℃±5℃ For 5~10 Second



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

Ordering Information

2343 01 XX X N XX S U X 0X

No.of
Pins
NPin
N=02~40

Insulator Material
Option
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP

Contact Plating
G1:Gold Flash
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Packing
A=Tray
T=Tube
P=Tube+Cap
R=Reel+Cap
M=Reel+Mylar

JILN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5992

PART NO. 234301XXXNXXSUX0X

TITLE: 2.0PF H4.30mm 1xNpin 180°

				OPERATION		DRAW	yiyusheng	20.10.20	SCALE	FIT	JILN ® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5992	
				X.X	±0.30				UNIT	mm		
A	A0	2020.10.20	NEW DRAWING	X.XX	±0.20	CHECK			SIZE	A4		
				X.XXX	±0.10				SHEET	1/1		
				Angle	±3°	APPROVE			PROJ.	Φ		
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL						