




Recommended P.C.B Layout
General Tolerance±0.05



Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance:30mΩ Max

接触电阻: 30mΩ Max

X1501 W R S - 2xXX - LP XX
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Range:R-Stright 90°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:2xXX-2x05~2x20 Pin
- 6.Material:LP-LCP 94V-0 (Gray)
- 7.Plating:V01-Gold Flash ; SN-Plated Tin

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x05	6.00	11.20	2x13	18.00	23.20
2x06	7.50	12.70	2x14	19.50	24.70
2x07	9.00	14.20	2x15	21.00	26.20
2x08	10.50	15.70	2x16	22.50	27.70
2x09	12.00	17.20	2x17	24.00	29.20
2x10	13.50	18.70	2x18	25.50	30.70
2x11	15.00	20.20	2x19	27.00	32.20
2x12	16.50	21.70	2x20	28.50	33.70

















X1501WRS-2xXX-LPXX	LCP	Phosphor Bronze	X1501H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector	
DWN		VIEW:	PART NO.: X1501WRS-2xXX-LPXX	
CHKD		UNIT: mm/in	DWG NO.: X-X1501WRS-2xXX-LPXX	
APPD		SIZE: A4		
			WEIGHT	SHEET
				1/1
			REVISION	A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED



							DSND		SCALE: N/A		MODEL TYPE: 1.5mm Crimp Style Connector			
ΔX					ANGLAR	$\pm 5^{\circ}$		DWN		VIEW: 	PART NO.: X1501WRS-2xXX-LPXX			
ΔX					$L \leq 4$	± 0.2		CHKD		UNIT: mm/in	DWG NO.: X-X1501WRS-2xXX-LPXX			
ΔX					$4 < L \leq 16$	± 0.3		APPD		SIZE: A4				
ΔX					$16 < L \leq 63$	± 0.4								
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5								
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET 1/1	REVISION A0
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														