






MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	ø1.65	ø2.0	ø2.5
APPD.			

DC-005	DC-005-1

SCHEMATIC

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ±0.1	ANGULAR	A1	2019.12.18	更新开孔图尺寸		GYW	
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
6	DC005 PING	BRASS	1	Ni PLATED	TITLE:DC JACK			UNIT : MM	ROHS COMPLIANT	DWN		
5	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED	MODEL:DC-005 -2.0-SU			SCALE: 4:1	CHK'D			
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED					APPD			
3	DC005 3#SPRING	SUS/PBS	1	Ag PLATED								
2	DC005 COVER	PBT	1	BLACK/WHITE								
1	DC005 CASE	PBT/PA6T+PA66	1	BLACK/WHITE								
NO.	PART NAME	MATERIAL	QTY	FINISHING								

东莞市六钩电子五金有限公司

PRO.AGL: REV :A1