






SPECIFICATIONS

Rated Current:2.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:800MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Max.Processing Temp:
(PBT)245°C±5°C For 5~10 Second
(PA6T/LCP)260°C±5°C For 5~10 Second



Ordering Information

3320 XX R XX X B M X XX

No.of Pins
NPin
N=02~40

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:tin

Insulator Material
Option
A=BK-PBT
C=BK-PA6T
F=BK-LCP

Color Type
B=Black

Latch Type
M=Middle Latch

Packing
O=PE Bag
A=Tray
T=Tube

Code Stream

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

				OPERATION		DRAW	Jelly Feng	2023.07.14	SCALE	FIT	JILN®深圳锦凌电子股份有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
				X.XXX	±0.10				SHEET	1/1		
A0	2023.07.14	NEW DRAWING			Angle	APPROVE			PROJ.		PART NO.	3320XXRXXBMXXX
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM				TOL	TITLE:	2.0 ejector header NPin 90° Middle Latch	