






HAOYU



PIN	Ø2.0	Ø2.5
APPD.		

注力度要求: 插力11N-20N, 拔力12-20N.  
(常规不带凹槽插头)

NO.	PART NAME	MATERIAL	QTY	CE		TITLE:DC JACK	MODEL: DC-005Q-2.0-SU	ROHS COMPLIANT	CHK'D	A	REV: A3
				ABOVE 5mm: ±0.2	ANGULAR ±1°						
6	DC005 PING	BRASS	1	Ni PLATED							
5	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED							
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED							
3	DC005Q 3#SPRING	SUS	1	Ag PLATED							
2	DC005 COVER	PBT	1	YELLOW/BLACK/RED							
1	DC005 CASE	PBT/PA66+PA6T	1	YELLOW/BLACK/RED							

东莞市六钧电子五金有限公司