




PCB LAYOUT



Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+85℃

温度范围: -40℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:3.5mΩ Max

接触电阻: 3.5mΩ Max

X1502 W V - XX - 46 XXX  
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:V-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~20 Pin
- 5.Material:46-PA46 UL94V-0
- 6.Plating:V01-Gold 1u" ;V03-Gold 3u"

| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 02    | 1.50           | 4.50  | 09    | 12.00          | 15.00 |
| 03    | 3.00           | 6.00  | 10    | 13.50          | 16.50 |
| 04    | 4.50           | 7.50  | 11    | 15.00          | 18.00 |
| 05    | 6.00           | 9.00  | 12    | 16.50          | 19.50 |
| 06    | 7.50           | 10.50 | 13    | 18.00          | 21.00 |
| 07    | 9.00           | 12.00 | 20    | 28.50          | 31.50 |
| 08    | 10.50          | 13.50 | /     |                |       |

|                  |          |               |                      |
|------------------|----------|---------------|----------------------|
| X1502WV-XX-46XXX | PA46     | Brass         | X1502H               |
| PART NO          | Material | Material(Pin) | Suitable XKB Housing |

|                                      |  |             |                                            |
|--------------------------------------|--|-------------|--------------------------------------------|
| DSND                                 |  | SCALE: N/A  | MODEL TYPE:<br>1.5mm Crimp Style Connector |
| DWN                                  |  | VIEW:       | PART NO.:<br>X1502WV-XX-46XXX              |
| CHKD                                 |  | UNIT: mm/in | DWG NO.:<br>X-X1502WV-XX-46XXX             |
| APPD                                 |  | SIZE: A4    |                                            |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |  |             | WEIGHT                                     |
|                                      |  |             | SHEET                                      |
|                                      |  |             | REVISION                                   |
|                                      |  |             | 1/1                                        |
|                                      |  |             | A0                                         |

XKB

广东星坤科技股份有限公司

|       |             |
|-------|-------------|
| Δ*    | 日期          |
| Δ*    | 日期          |
| Δ*    | 日期          |
| MARK  | DESCRIPTION |
| 文件工程章 |             |

|                                               |  |  |  |  |          |                        |
|-----------------------------------------------|--|--|--|--|----------|------------------------|
|                                               |  |  |  |  | ANGLAR   | ±5°                    |
|                                               |  |  |  |  | L≤ 4     | ±0.2                   |
|                                               |  |  |  |  | 4<L≤ 16  | ±0.3                   |
|                                               |  |  |  |  | 16<L≤ 63 | ±0.4                   |
|                                               |  |  |  |  | L> 63    | ±0.5                   |
| REVISIONS                                     |  |  |  |  |          | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |          |                        |