





SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

1225 11 XX X N XX R XXX X XX

No. of Pins
01~40P
Insulator
Option
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP
Material
Contact
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin
Plating
Pin Length
Packing
0=PE Bag
A=Tray
code stream
01~99



Dimension antitheses list

ITEM	PA	PB	PC
Standard	6.00	4.40	3.00

OPERATION

DRAW

YiYuSheng

12.04.18

SCALE

FIT

JILN 深圳锦凌电子股份有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD
Tel: 86-755-27483253 Fax: 86-755-2997-5588

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

APPROVE

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

1/1

PART NO.

122511XXXNXXRXXXXXX

TITLE:

2.54PH H2.5mm 1xNpin 90°

A

A