



SPECIFICATIONS

Current Rating:3.0AMP

Contact Resistance:10mΩ Max

Dielectric Strength:Min 1000V RMS

Mating Pin:ø0.4 to ø0.56mm

Forces:(polished steel gauge ø0.43mm)

Operation Temperature:-40°c to +105°c

Sleeve:Brass





Contact Plating:Au Over Ni

Contact Clip(4 finger):Phosphor Bronze/BeCu

Insulator Material:Polyester(UL94V-0)

Standard: PPS

Soldering Temperature: 260°C±5° 5S



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

Ordering Information

3620 30 2 XX S XX 074 0X

No.of Pins
Per Row
2~40

Contact Plating
G0:Gold Flash
S0:Gold Flash/Tin

Length
074=7.43mm

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

yiyusheng

17.08.05

SCALE

FIT

UNIT mm

SIZE A4

SHEET 1/1

PROJ.

JILN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5588

PART NO.

3620302XXSXX0740X

TITLE:

2.54x3.0圆孔母座 180° L=7.43

A0 2017.08.05 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE