





HAOYU



PIN	Ø2.0	Ø2.5
APPD.		

注力度要求: 插力11N-20N, 拔力12-20N.  
(常规不带凹槽插头)

				CE	
				A3 2020.8.07 3 依据历史生产数据修正尺寸4.2至4.6	GYW
				A2 2016.6.20 2 增加重点尺寸	
6	DC005 PING	BRASS	1	Ni PLATED	
5	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED	
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED	
3	DC005Q 3#SPRING	SUS	1	Ag PLATED	
2	DC005 COVER	PBT	1	YELLOW/BLACK/RED	
1	DC005 CASE	PBT/PA66+PA6T	1	YELLOW/BLACK/RED	
NO.	PART NAME	MATERIAL	QTY	FINISHING	

ABOVE 5mm: ±0.2	ANGULAR ±1°	NO	TITLE:DC JACK	ROHS COMPLIANT	CHK'D		
			MODEL: DC-005Q-2.0-SU-B				
						A	REV: A3

东莞市六钧电子五金有限公司