





SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

1225 11 XX X N XX S XXX X XX

No.of Pins
01~40P



Insulator
Option
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP

Material
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Contact Plating
Pin Length

Packing
0=PE Bag
A=Tray
T=Tube
P=Tube+Cap
R=Reel+Cap

code stream
01~99



Dimension antitheses list

ITEM	PA	PC
Standard	6.00	3.00

JILN® 深圳锦凌电子股份有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD
Tel: 86-755-27483253 Fax: 86-755-2997-5588

PART NO. 122511XXXNXXSXXXXXX

TITLE: 2.54PH H2.5mm 1xNpin 180°

OPERATION

DRAW

YiYuSheng

12.04.18

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

☞

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

CHECK

APPROVE

A0 2012.04.18 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9