



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

Current Rating:	3Amps
Insulation Resistance:	1000MΩ Min
Contact Resistance:	20mΩ Max
Withstanding Voltage:	AC 1000V
Operation Temperature:	−40° to+105°
Contact Material:	Brass
Standard:	PA6T
Insrlator Material:	Polyester(UL 94V−0)
Contact Plating:	Gold Flash
Max.Processing Temp:	240°C for30−60seconds (260°C for5seconds)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO.	TITLE:		
.XX ±0.20	X.X° ±1°	B25411210-APB0513-H25A60	2.54PH H2.5 2xnPin 90度 PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 李四面		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1