








参考安装方式

NOTES:

备注

1.Copper,nickel base,matte tin

黄铜H62, 镍底, 镀雾锡

2.Wire screw hole M4

压线螺孔M4

3.Current Rating: 50A

额定电流: 50A

4.Operating temperature: -40℃ ~ +125℃

工作温度: -40℃ ~ +125℃

5.There shall be no defects such as pin deformation and burrs.

不得有脚变形, 毛刺等缺陷


6.Unmarked dimensions refer to tolerances

未标注的尺寸参考公差

Ordering Information

XD - * * * * - * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	Dip	Product No.	Material
M=Full Teeth (插针)	3=M3 (螺孔)	2=2个 (焊脚)	(防止扭动)	0808=8x8mm	S=Sn (焊脚)	产品序号	默认=Copper (黄铜)
RN=Silver Nut (螺母)	4=M4 (螺孔)	4=4个 (焊脚)		1014=10x14mm	F=Flag Dip		IC=Red Copper (紫铜)
G=Silver Gasket (垫片)	5=M5 (螺孔)	6=6个 (焊脚)					
	6=M6 (螺孔)	8=8个 (焊脚)					



GENERAL TOLERANCE

制图

02

DIM TOL

审核

X.X ±0.30

批准

X.XX ±0.20

比例

X.XXX ±0.10

SCALE

Angle ±3.0°

投影



深圳讯答科技有限公司

ShenzhenXunDaTechnology Co.,Ltd

产品名称

PCB 焊接端子 (插板 铜垫片 M4 4焊脚 8x8x8.2mm)

版本

A

产品料号

XD-RG44-0808-D052-02

单位

mm

材料

页次

1/1