




参考安装方式

NOTES:

备注

1.Copper,nickel base,matte tin

黄铜H62, 镍底, 镀雾锡

2.Wire screw hole M4

压线螺孔M4

3.Current Rating: 60A

额定电流: 60A

4.Operating temperature: -40°C ~ +125°C


工作温度: -40°C ~ +125°C

5.There shall be no defects such as pin deformation and burrs.

不得有脚变形, 毛刺等缺陷

6.Unmarked dimensions refer to tolerances

未标注的尺寸参考公差



Ordering Information

XD - * * * * - **** - D *** * - 02

Type	Screw	Welding	T=Anti	Series	D=DIP	Product No.	Material
M=Full Teeth (插牙)	Thread 3=M3 (螺牙)	Feet 4=M4 (螺牙)	Twist (防止扭动)	0808=8x8mm 1014=10x14mm	S=SMT FD=Flag DIP	产品序号	默认=Copper (黄铜) RC=Red Copper (紫铜)
R=Pin Nut (铆螺母)	5=M5 (螺牙)	4=4个					
RG=Rivet Gasket (铆垫片)	6=M6 (螺牙)	6=6个					
	8=M8 (螺牙)	8=8个					



GENERAL TOLERANCE

制图

02



深圳讯答科技有限公司
ShenzhenXunDaTechnology Co.,Ltd

DIM TOL

审核

产品名称

PCB 焊接端子 (插板 铆垫片 M4

版本

A

X.X ±0.30

批准

4焊脚 10x10.5x13.9mm 四脚防扭)

REV.

mm

X.XX ±0.20

比例

产品料号

XD-RG44T-1010-D056-02

单位

UNIT

X.XXX ±0.10

SCALE

PART NO.

材料

页次

1/1

Angle ±3.0°

投影

MATERIAL

SHEET

1/1

初版发行

变更内容

日期

MODIFY CONTENT

MODIFY DATE

序号

No.